




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F9	REVISED PER ECN-23-240910	29NOV2023	WLS	VS
	F10	REVISED PER ECN-24-279340	04SEP2024	WLS	JP



- 1 MATERIAL: HOUSING - UL 94V-0 RATED HIGH TEMP. NYLON, COLOR BLACK.
CONTACT - BRASS.
HOLDDOWNS - PHOSPHOR BRONZE.
 - 2 MAXIMUM INSERTION 30 LBS.
 - 3 RECOMMENDED BOARD THICKNESS 1.57.
 - 4 FINISH: CONTACT - 0.76 μ m MINIMUM GOLD ON MATING AREA.
2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS.
ALL OVER 1.27 μ m NICKEL MINIMUM.
HOLDDOWNS - 2.54 μ m MATTE TIN OVER 1.27 μ m NICKEL MINIMUM.
 - 5 CUTTING AREA REGION, NO PLATING IS PRESENT.
- 6 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION).
- 7 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE OBSOLETE OBSOLETE OBSOLETE	40.00	33.00	37.30	36.86	24	5-794682-4
	37.00	30.00	34.30	33.86	22	5-794682-2
	34.00	27.00	31.30	30.86	20	5-794682-0
	31.00	24.00	28.30	27.86	18	4-794682-8
	28.00	21.00	25.30	24.86	16	4-794682-6
	25.00	18.00	22.30	21.86	14	4-794682-4
	22.00	15.00	19.30	18.86	12	4-794682-2
	19.00	12.00	16.30	15.86	10	4-794682-0
	16.00	9.00	13.30	12.86	8	3-794682-8
	13.00	6.00	10.30	9.86	6	3-794682-6
	10.00	3.00	7.30	6.86	4	3-794682-4
	7.00	-	4.30	3.86	2	3-794682-2
DIM A	DIM Z	DIM Y	DIM X	NO. OF POSN.	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER 16AUG99 CHK K. COBLE 16AUG99 APVD K. COBLE 16AUG99		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.20 3 PLC ± 4 PLC ± ANGLES ±1°		NAME VERTICAL HEADER ASSEMBLY, THRU HOLE, 30 GOLD, DUAL ROW, MICRO MATE-N-LOK™	
		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000			
MATERIAL		FINISH 			
		WEIGHT -		SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING				DRAWING NO C=794682	RESTRICTED TO -
				SCALE 4:1	SHEET 1 OF 2
				REV F10	

