




REVISIONS				
P.	LTN.	DESCRIPTION	DATE	APVD.
H		REVISED PER ECR-17-015775	03NOV2017	BDA KR
J		REVISED PER ECR-21-101886	03MAY2021	PC JS






3-DIMENSIONAL MODEL
SCALE 2:1



RECOMMENDED CUT OUT
SCALE 2:1

- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
 - RECOMMENDED PANEL THICKNESS 0.76 - 2.29 [0.030 - .090].
 - PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
 - DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED CONDITION ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- UL AND CSA LOGOS LOCATED APPROXIMATELY AS SHOWN



BLACK	1-794762-9
GRAY	1-794762-8
BLUE	1-794762-6
GREEN	1-794762-5
YELLOW	1-794762-4
ORANGE	1-794762-3
RED	1-794762-2
BROWN	1-794762-1
RED	794762-3
NATURAL	794762-1
COLOR	PART NUMBER

SUPERSEDED BY 794762-3

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN: K. WHITAKER 20-JUNE-2000
 CHK: K. COBLE 20-JUNE-2000
 APVD: K. COBLE 20-JUNE-2000

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm [INCHES]		0 PLC	±
		1 PLC	±0.511 (0.020)
		3 PLC	±
		4 PLC	±
		ANGLES	±0° 30'

MATERIAL: NYLON, UL 94V-0, WHITE

PRODUCT SPEC: CAP. 12 CIRCUIT, UNIVERSAL MATE-N-LOK(TM), SPECIAL

APPLICATION SPEC: A1 00779 C=794762

WEIGHT: CUSTOMER DRAWING

SCALE: 4:1 SHEET: 1 OF 1 REV: J