



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			3	REVISED PER ECO-09-023313	10OCT09	AEG	-
			4	ECR-10-001372	10MAR10	RK	SRE
			5	ECR-10-025774	20JAN11	KK	HMR

POLZ.	L±0.5	BESTELL-NR.
1	3.3	826-544-1
2	7.3	
3	11.3	
4	15.2	
5	19.2	
6	23.1	
7	27.1	
8	31.1	
9	35.1	
10	39.0	1
11	43.0	1
12	46.9	1
13	50.9	1
14	54.8	1
15	58.8	1
16	62.8	1
17	66.7	1
18	70.7	1
19	74.7	1
20	78.6	2
21	82.6	2
22	86.5	2
23	90.5	2
24	94.4	2
25	98.4	2
26	102.4	2
27	106.3	2
28	110.3	2
29	114.2	2
30	118.2	3
31	122.2	3
32	126.1	3
33	130.1	3
34	134.0	3
35	138.0	3
36	141.6	3-826 544-6

ZEICHNUNG GÜLTIG AB 20/90



BOHRBILD



- 1 STECKSEITE: IM BEREICH "F" 0.8 μm GOLD ÜBER 1.27 μm NICKEL IM BEREICH "B"
- 2 LÖTSEITE: MIN. 2.5 μm ZINN ÜBER 1.27 μm NICKEL
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 3 OBSOLETE

KONTAKTSTIFT	Cu Zn	1
STIFTGEHÄUSE	PBTP GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. VERWENDET FÜR

DIMENSIONS: mm

DWN	S.RIEGER	11.12.84	MATERIAL	-	FINISH	-	
CHK	SCHAARSCHMIDT	11.12.84	TE Connectivity				
APVD	-	-					
PRODUCT SPEC	NAME					AMP MODU I STIFTL. RASTER 3.96 EINREIHIG	
APPLICATION SPEC	SIZE					A4	
WEIGHT	CAGE CODE					00779	
CUSTOMER DRAWING						DRAWING NO	C-826544
SCALE						4:1	
SHEET						1 OF 1	
REV						5	

TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3mm

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -