






P	LTR	DESCRIPTION	DATE	DWN	APVD
	E3	REVISED PER ECO-11-004587	11MAR2011	RK	HMR
	E4	PART STATUS UPDATED	05JUL2021	SB	SS



- ① MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: GREEN.
TERMINAL: PHOSPHOR BRONZE, PLATING: SEE TABLE, OVER 2-3μm NICKEL
2. SUITABLE FOR 1,6-2, 4mm PC BOARD THICKNESS.
3. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE No. E60677.
4. IMQ CERTIFICATE WITH SURVEILLANCE ON CONFORMITY
WITH IEC 998-1/998-2-1.
- ⑤ INK MARKING, COLOR: WHITE.
- ⑥ LABEL APPLIED OR INK MARKING AS SHOWN.

OBSOLETE	0.76 μm GOLD	-	-	60.60	55.88	10	2-796859-6
	0.2 μm GOLD		DETAIL G	35.20	30.48	5	2-796859-5
	TIN		DETAIL F	25.04	20.32	3	2-796859-4
um NICKEL	TIN	-	-	126.64	121.92	23	2-796859-3
	TIN	-	-	121.56	116.84	22	2-796859-2
	TIN	-	-	116.48	111.76	21	2-796859-1
	TIN	-	-	111.40	106.68	20	2-796859-0
	TIN	-	-	106.32	101.60	19	1-796859-9
	TIN	-	-	101.24	96.52	18	1-796859-8
	TIN	-	-	96.16	91.44	17	1-796859-7
	TIN	-	-	91.08	86.36	16	1-796859-6
	TIN	-	-	86.00	81.28	15	1-796859-5
	TIN	-	-	80.92	76.20	14	1-796859-4
	TIN	-	-	75.84	71.12	13	1-796859-3
	TIN	-	-	70.76	66.04	12	1-796859-2
	TIN	-	-	65.68	60.96	11	1-796859-1
	TIN	-	-	60.60	55.88	10	1-796859-0
	TIN	-	-	55.52	50.80	9	796859-9
	TIN	-	-	50.44	45.72	8	796859-8
	TIN	-	-	45.36	40.64	7	796859-7
	TIN	-	-	40.28	35.56	6	796859-6
	TIN	-	-	35.20	30.48	5	796859-5
	TIN	-	-	30.12	25.40	4	796859-4
	TIN	-	-	25.04	20.32	3	796859-3
	TIN	-	-	19.96	15.24	2	796859-2

TERMINAL PLATING		MARKING		SPECIAL		L		H		NO. OF POSN		PART NUMBER			
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN S. WELDON 12FEB2001		STE TE Connectivity									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK D. BIEVENOUR 12FEB2001											
		0 PLC ±		APVD D. BIEVENOUR 12FEB2001		NAME TERMINAL BLOCK, PLUG 90 DEGREE, WITH FLANGE, 5.08mm PITCH									
		1 PLC ±0.2		PRODUCT SPEC											
		3 PLC ±0.00		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
		4 PLC ±0.000		-		A2		00779		C=796859					
MATERIAL		FINISH		WEIGHT											
				-											
CUSTOMER DRAWING										SCALE 4:1		SHEET 1 OF 2		REV F4	

4


3

2


1

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



DETAIL F



DETAIL G

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON	12FEB2001	 TE Connectivity		
DIMENSIONS:		CHK D. BIEVENOUR	12FEB2001			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. BIEVENOUR	12FEB2001	NAME TERMINAL BLOCK, PLUG 90 DEGREE, WITH FLANGE, 5.08mm PITCH		
	0 PLC ±-	PRODUCT SPEC				
	1 PLC ±0.2	-				
	2 PLC ±0.00	APPLICATION SPEC				
	3 PLC ±0.000	-				
	4 PLC ±0.0000	SIZE				
	ANGLES ±-	CAGE CODE				
MATERIAL	FINISH	DRAWING NO		RESTRICTED TO		
		WEIGHT		A200779		
		CUSTOMER DRAWING		C=796859		
				SCALE		
				4:1		
				SHEET		
				2 OF		
				REV	E 4	