



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECN-23-230183	07SEP2023	DW	JH




- NOTE : UNLESS OTHERWISE SPECIFIED
- FABRICATE TO MEET IPC – 6012, CLASS 2.
INSPECT TO MEET IPC – A – 600, CLASS 2.
 - MATERIALS
 - ANTENNA MATERIAL : FR4 PCB, OVERALL THICKNESS 1.64±0.15mm
 - EVB MATERIAL : FR4 PCB, OVERALL THICKNESS 1.00mm
 - SMA(FEMALE) PANEL TYPE CONN. : 50 OHMS(IMPEDANCE)
 - MEASURED WITH MATCHING CIRCUIT CONDITIONS.
 - GENERAL TOLERANCES : ±0.20
 - PACKAGING : SINGULATED PARTS TO BE SECURELY SHRINK WARPPED, BAGGED OR VACUUM PACKED IN BULK
 - CONSULT TE CONNECTIVITY DATA SHEET DS2118614.
 - SILKSCREEN : WITHE EPOXY INK.
A: TE LOGO, TE P/N
B: WORD REV., FOLLOWED BY THE LASTEST REVISION LETTER. AS SHOWN.
C: 4 DIGITS DATE CODE: FIRST 2 DIGITS FOR THE WEEK CODE AND THE 2 DIGITS FOR THE YEAR CODE.
OTHERS: SPECIFIC TE INTERNAL USE ONLY.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW.PARK	17AUG2022	 TE Connectivity		
		CHK H.SHIN	17AUG2022			
		APVD CY.PARK	17AUG2022	NAME 2118614-1 ANTENNA WITH EVB ASSY		
		PRODUCT SPEC —				
		APPLICATION SPEC —				
		WEIGHT —		SIZE A3	CAGE CODE 00779	DRAWING NO C-8-2118614
		CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 2	REV A1


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




8-2118614-1



BUFFER SPONGE




INDIVIDUAL BOX





1 PC/1 Individual Box

Induividual box Label



100 PCS Individual Box / 1 Carton Box



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW.PARK 17AUG2022		TE Connectivity				
		CHK H.SHIN 17AUG2022						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 2118614-1 ANTENNA WITH EVB ASSY				
		APVD CY.PARK 17AUG2022						
		PRODUCT SPEC —						
		APPLICATION SPEC —						
		WEIGHT —						
MATERIAL —		FINISH —		SIZE A3	CAGE CODE 00779	DRAWING NO C-8-2118614	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 1:1	SHEET 2 OF 2	REV A1