



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F1	PART OBSOLESCENCE	11JUL2024	AR	VG

BOHRBILD:

FÜR FA. RHODE & SCHWARZ



BEI LEITUNGSDURCHFÜHRUNGEN ZWISCHEN DEN KONTAKTEN
BOHRUNGSDURCHMESSER $0.95^{+0.1}$ MIT LÖTAUGE $\varnothing 1.5$




- ⚠ MIN. 3µm TIN OVER 1.27µm NICKEL
- ⚠ OBSOLETE

CONTACT PIN	CuZn	⚠
PIN HOUSING	PCT	BLACK
DESCRIPTION	MATERIAL	COLOR/ FINISH

TE Connectivity. All Rights Reserved.



POS.	L-1.0	PART NUMBER
-	-	-1- ⚠
2	5.08	827314-2- ⚠
3	7.62	-3- ⚠
4	10.16	-4- ⚠
5	12.70	-5- ⚠
6	15.24	-6- ⚠
7	17.78	-7- ⚠
8	20.32	-8- ⚠
9	22.86	-9- ⚠
10	25.40	-0- ⚠
11	27.94	-1- ⚠
12	30.48	-2- ⚠
13	33.02	-3- ⚠
14	35.56	-4- ⚠
15	38.10	-5- ⚠
16	40.64	-6- ⚠
17	43.18	-7- ⚠
18	45.72	-8- ⚠
19	48.26	-9- ⚠
20	50.80	-0- ⚠
21	53.34	-1- ⚠
22	55.88	-2- ⚠
23	58.42	-3- ⚠
24	60.96	-4- ⚠
25	63.50	-5- ⚠
26	66.04	-6- ⚠
27	68.58	-7- ⚠
28	71.12	-8- ⚠
29	73.66	-9- ⚠
30	76.20	-0- ⚠
31	78.74	-1- ⚠
32	81.28	-2- ⚠
33	83.82	-3- ⚠
34	86.36	-4- ⚠
35	88.90	-5- ⚠
36	91.44	-6- ⚠
37	93.98	-7- ⚠
38	96.52	-8- ⚠
39	99.06	-9- ⚠
40	101.60	-0- ⚠
41	104.14	-1- ⚠
42	106.68	-2- ⚠
43	109.22	-3- ⚠
44	111.76	-4- ⚠
45	114.30	-5- ⚠
46	116.84	-6- ⚠
47	119.38	-7- ⚠
48	121.92	-8- ⚠
49	124.46	-9- ⚠
50	127.00	-0- ⚠

DIMENSIONS:		DWN	10.04.79	MATERIAL		SEE TABLE		FINISH		SEE NOTE 1	
mm		CHK	12.04.79	TE Connectivity							
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm		APVD	—								
0 PLC	± —	PRODUCT SPEC		NAME AMPMODU II PIN HEADER, 90 DEG SINGLE ROW							
1 PLC	± —	108—18012									
2 PLC	± —	APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
3 PLC	± —	—		A4		00779		C—827314		—	
4 PLC	± —	WEIGHT		CUSTOMER DRAWING							
ANGLES	± —										
		SCALE 4:1									
		SHEET 1 OF 1									
		REV F1									