TWO CONDUCTOR CABLE, SHIELDED, JACKETED, GENERAL PURPOSE, FLEXIBLE, 600 VOLT

Date 5-15-07 Rev

This specification sheet forms a part of the latest issue of Raychem Specification 80.

evision E

COMPONENT WIRES - 81A0111 SHIELD - TIN-COATED COPPER JACKET - RADIATION-CROSSLINKED, MODIFIED FLEXIBLE ETFE

CABLE CONSTRUCTION DETAILS							
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	(lbs/1000 ft.)
81A1121-26-*	26	38	.006	.009	.097	.102	8.2
81A1121-24-*	24	38	.006	.009	.107	.112	10.1
81A1121-22-*	22	38	.007	.010	.121	.127	13.0
81A1121-20-*	20	38	.007	.010	.139	.146	17.5
81A1121-18-*	18	38	.007	.011	.161	.169	24.1
81A1121-16-*	16	38	.008	.012	.177	.186	29.4
81A1121-14-*	14	38	.009	.013	.209	.219	41.7
81A1121-12-*	12	38	.010	.015	.257	.270	61.7
81A1121-10-*	10	38	.012	.018	.315	.331	94.5
81A1121- 8-*	8	36	.015	.023	.447	.469	172.
81A1121- 6-*	6	36	.018	.027	.549	.576	257.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C
Maximum continuous conductor temperature
VOLTAGE RATING: 600 volts (rms) at sea level
CROSSLINKING PROOF TEST: 300 ± 3°C for 7 hours
DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz
JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 100% (minimum)

Tensile Strength, 3000 lbf/in² (minimum)

JACKET FLAWS:

Spark Test, 1500 volts (rms) Impulse Dielectric Test, 6.0 kV (peak)

NOTE: Nominal values are for information only. Nominal values are not requirements.

SECANT MODULUS (Test per ASTM D 882): 4.0 x 10⁴ lbf/in² (maximum),

2% strain, 2 inch jaw separation, 0.2 inch/minute SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND (Post Environmental):

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

1/ Example: AWG 10, black and brown component wires; white jacket: 81A1121-10-0/1-9

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 1

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL

RAYCHEM is a trademark of Tyco Electronics Corporation.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297