


THIS DRAWING IS UNPUBLISHED
 RELEASED FOR PUBLICATION 2007
 © COPYRIGHT 2007 ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-	G2	REVISED PER ECO-09-025714	16DEC09	KK AEG
		G3	REVISED PER ECR-10-025774	04MAY11	KK HMR

POS. PER ROW	L +0.3 -0.6	PART - NO.	POS. PER ROW	L +0.3 -0.6	PART - NO.
-	-	-	26	66.04	2- 827 363-6
2	5.08	827 363-2	27	68.58	2- -7
3	7.62	-3	28	71.12	2- -8
4	10.16	-4	29	73.66	2- -9
5	12.70	-5	30	76.20	3- -0
6	15.24	-6	31	78.74	3- -1
7	17.78	-7	32	81.28	3- -2
8	20.32	-8	33	83.82	3- -3
9	22.86	-9	34	86.36	3- -4
10	25.40	1- -0	35	88.90	3- -5
11	27.94	1- -1	36	91.44	3- -6
12	30.48	1- -2	37	93.98	3- -7
13	33.02	1- -3	38	96.52	3- -8
14	35.56	1- -4	39	99.06	3- -9
15	38.10	1- -5	40	101.60	4- -0
16	40.64	1- -6	41	104.14	4- -1
17	43.18	1- -7	42	106.68	4- -2
18	45.72	1- -8	43	109.22	4- -3
19	48.26	1- -9	44	111.76	4- -4
20	50.80	2- -0	45	114.30	4- -5
21	53.34	2- -1	46	116.84	4- -6
22	55.88	2- -2	47	119.38	4- -7
23	58.42	2- -3	48	121.92	4- -8
24	60.96	2- -4	49	124.46	4- -9
25	63.50	2-827 363-5	50	127.00	5- 827 363-0



- 1 0.8 μm GOLD OVER 1.27 μm NICKEL (PRE-GOLD PLATED)
0.8 μm GOLD ÜBER 1.27 μm NICKEL (VORVERGOLDET)
- 2 PIN TIPS PARTIALLY WITHOUT SURFACE
STIFTSPITZEN TEILWEISE BLANK
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 4 OBSOLETE

PC BOARD LAYOUT
LEITERPLATTENANSCHLUSSBILD



1	CONTACT PIN KONTAKTSTIFT	Cu Sn
COLOUR GREEN	PINHOUSING STIFTGEHAEUSE	PBT GV
REMARK	DESCRIPTION BEZEICHNUNG	MATERIAL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PFEIFER 02NOV1981	TE Connectivity	
		CHK KOURIMSKY 06NOV1981		
DIMENSIONS: mm		APVD -	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-18012	AMPMODU II PINHEADER SINGLE ROW STIFTLAISTE EINREIHIG	
0 PLC ±0.2		APPLICATION SPEC -	SIZE A3	CAGE CODE 00779
1 PLC ±0.2		WEIGHT -	DRAWING NO C-827363	RESTRICTED TO -
2 PLC ±0.2		CUSTOMER DRAWING		
3 PLC ±		SCALE 5:1	SHEET 1 OF 1	REV G3
4 PLC ±				
ANGLES ±2°				
FINISH -				