


USED FOR
E 75-9233

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F3	PART OBSOLESCENCE	01JUL2024	RS	VG

POS.	L±0.5	PART NO
-	-	-
2	5.08	825435 -2
3	7.62	-3 Δ 3
4	10.16	-4
5	12.70	-5 Δ 3
6	15.24	-6 Δ 3
7	17.78	-7
8	20.32	-8 Δ 3
9	22.86	-9 Δ 3
10	25.40	-10 Δ 3
11	27.94	-11 Δ 3
12	30.48	-12 Δ 3
13	33.02	-13 Δ 3
14	35.56	-14 Δ 3
15	38.10	-15 Δ 3
16	40.64	-16 Δ 3
17	43.18	-17 Δ 3
18	45.72	-18 Δ 3
19	48.26	-19 Δ 3
20	50.80	-20 Δ 3
21	53.34	-21 Δ 3
22	55.88	-22 Δ 3
23	58.42	-23 Δ 3
24	60.96	-24 Δ 3
25	63.50	-25 Δ 3
26	66.04	-26 Δ 3
27	68.58	-27 Δ 3
28	71.12	-28 Δ 3
29	73.66	-29 Δ 3
30	76.20	-30 Δ 3
31	78.74	-31 Δ 3
32	81.28	-32 Δ 3
33	83.82	-33 Δ 3
34	86.36	-34 Δ 3
35	88.90	-35 Δ 3
36	91.44	-36 Δ 3
37	93.98	-37 Δ 3
38	96.52	-38 Δ 3
39	99.06	-39 Δ 3
40	101.60	-40 Δ 3
41	104.14	-41 Δ 3
42	106.68	-42 Δ 3
43	109.22	-43 Δ 3
44	111.76	-44 Δ 3
45	114.30	-45 Δ 3
46	116.84	-46 Δ 3
47	119.38	-47 Δ 3
48	121.92	-48 Δ 3
49	124.46	-49 Δ 3
50	127.00	5- 825435 -0



- 1 MATING SIDE: Min 0.76µm (PdNi + Au FLASH) IN ZONE "F"
OVER Min 1.27µm Ni
(Alternative plating - Min 0.76µm Au OVER Min 1.27µm Ni)
SOLDER SIDE: 3-5µm TIN OVER Min 1.27µm NICKEL
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 3 OBSOLETE


CONTACT PIN	CuZn	Δ 1
PEN HOUSING	PBT GV	GREEN
DESCRIPTION	MATERIAL	SURFACE COLOR

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
±0.2mm

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -



DWN

A.HO

11APR1984

CHK

M.SCHAARSCHMIDT

11APR1984

APVD

-

PRODUCT SPEC

108-18012

APPLICATION SPEC

-

WEIGHT

-

MATERIAL

-

FINISH

-

TE

TE Connectivity

NAME

AMPMODU II PIN HEADER, SINGLE ROW

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-825435

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

4:1

SHEET

1 OF 1

REV F3