


REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
	G2	PART OBSOLESCENCE	31JUL2024	RS
				VG

POS. PER ROW	L±0.5	PART NUMBER.	
1	2.54	825440	-1
2	5.08	825440	-2
3	7.62		-3
4	10.16		-4
5	12.70		-5
6	15.24		-6
7	17.78		-7
8	20.32		-8
9	22.86		-9
10	25.40	1-	-0
11	27.94	1-	-1
12	30.48	1-	-2
13	33.02	1-	-3
14	35.56	1-	-4
15	38.10	1-	-5
16	40.64	1-	-6
17	43.18	1-	-7
18	45.72	1-	-8
19	48.26	1-	-9
20	50.80	2-	-0
21	53.34	2-	-1
22	55.88	2-	-2
23	58.42	2-	-3
24	60.96	2-	-4
25	63.50	2-	-5
26	66.04	2-	-6
27	68.58	2-	-7
28	71.12	2-	-8
29	73.66	2-	-9
30	76.20	3-	-0
31	78.74	3-	-1
32	81.28	3-	-2
33	83.82	3-	-3
34	86.36	3-	-4
35	88.90	3-	-5
36	91.44	3-	-6
37	93.98	3-	-7
38	96.52	3-	-8
39	99.06	3-	-9
40	101.60	4-	-0
41	104.14	4-	-1
42	106.68	4-	-2
43	109.22	4-	-3
44	111.76	4-	-4
45	114.30	4-	-5
46	116.84	4-	-6
47	119.38	4-	-7
48	121.92	4-	-8
49	124.46	4-	-9
50	127.00	5-	825440 -0

OBSOLETE



MATING SIDE: Min 0.76µm (PdNi + Au FLASH) IN ZONE "F"
OVER Min 1.27µm Ni
(Alternative plating - Min 0.76µm Au OVER Min 1.27µm Ni)
SOLDER SIDE: Min.2.5 µm TIN OVER Min 1.27µm NICKEL

CONTACT PIN	CuZn	
PIN HOUSING	PBT GV	GREEN
DESCRIPTION	MATERIAL	SURFACE
		COLOR

TE Connectivity. All Rights Reserved.



DIMENSIONS: mm	DWN M.SCHAARSCHMIDT	22JUN1984		MATERIAL	-	FINISH	-
	CHK	-					
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2 mm	APVD	-					
	PRODUCT SPEC	108-18012					
0 PLC ± -	APPLICATION SPEC	-					
1 PLC ± -	WEIGHT	-					
2 PLC ± -							
3 PLC ± -							
4 PLC ± -							
ANGLES ± -							
		TE Connectivity Ltd.		NAME AMPMODU II PIN HEADER, DUAL ROW			
		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		A4	00779	C-825440	-		
CUSTOMER DRAWING		SCALE	4:1	SHEET	1 OF 2	REV	G2

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

POS. PER ROW	L±0.5	PART NO.		REMARKS
1	2.54	5-	-1	
2	5.08	5-	-2	
3	7.62	5-	-3	
4	10.16	5-	-4	
5	12.70	5-	-5	
6	15.24	5-	-6	
7	17.78	5-	-7	
8	20.32	5-	-8	
9	22.86	5-	-9	
10	25.40	6-	0	
11	27.94	6-	-1	
12	30.48	6-	-2	
13	33.02	6-	-3	
14	35.56	6-	-4	
15	38.10	6-	-5	
16	40.64	6-	-6	
17	43.18	6- 825440	-7	 
18	45.72	6-	-8	
19	48.26	6-	-9	
20	50.80	7-	0	

 PACKAGING: 25 STUCK IN PLASTIC TIN
PN 165439-1 WITH PLASTIC LID
PN 165440-1


 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

 OBSOLETE

TE Connectivity. All Rights Reserved.

-



DIMENSIONS:		DWN	07JUN1984		MATERIAL		FINISH		
mm		A.HO		-					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	13JUN1984		 TE Connectivity Ltd.				
		M.SCHAARSCHMIDT							
		APVD	-		NAME AMPMODU II STIFTLEISTE ZWEIREIHIG				
		PRODUCT SPEC							
		APPLICATION SPEC							
0 PLC	± -	-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
1 PLC	± -	-		A4	00779	C-825440	-		
2 PLC	± -	-							
3 PLC	± -	-							
4 PLC	± -	-							
ANGLES	± -	-							
		WEIGHT	-						
		CUSTOMER DRAWING				SCALE	4:1	SHEET	2 OF 2