



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	PART OBSOLESCENCE	25JUN2024	RS	VG

WAR NR. 83-9738/1		
POLZ. PRO REIHE	L±0.4	BESTELL-NR.
1	-	1
2	5.08	2
3	7.62	3
4	10.16	4
5	12.70	5
6	15.24	6
7	17.78	7
8	20.32	8
9	22.86	9
10	25.40	10
11	27.94	11 827 932 1
12	30.48	12 827 932 2
13	33.02	13 827 932 3
14	35.56	14 827 932 4
15	38.10	15 827 932 5
16	40.64	16 827 932 6
17	43.18	17 827 932 7
18	45.72	18 827 932 8
19	48.26	19 827 932 9
20	50.80	20 827 932 0
21	53.34	21 827 932 1
22	55.88	22 827 932 2
23	58.42	23 827 932 3
24	60.96	24 827 932 4
25	63.50	25 827 932 5
26	66.04	26 827 932 6
27	68.58	27 827 932 7
28	71.12	28 827 932 8
29	73.66	29 827 932 9
30	76.20	30 827 932 0
31	78.74	31 827 932 1
32	81.28	32 827 932 2
33	83.82	33 827 932 3
34	86.36	34 827 932 4
35	88.90	35 827 932 5
36	91.44	36 827 932 6
37	93.98	37 827 932 7
38	96.52	38 827 932 8
39	99.06	39 827 932 9
40	101.60	40 827 932 0
41	104.14	41 827 932 1
42	106.68	42 827 932 2
43	109.22	43 827 932 3
44	111.76	44 827 932 4
45	114.30	45 827 932 5
46	116.84	46 827 932 6
47	119.38	47 827 932 7
48	121.92	48 827 932 8
49	124.46	49 827 932 9
50	127.00	50 829 235 0



- 4 OBSOLETE
- 3 PIN HEADER WEIGHT = 0,1323g x POS. PER ROW
- 2 Prod. Spec. 108-18012 , Appl.Spec. 114-25011
- 1 MIN. 2.0µm ZINN ÜBER 1.27µm NICKEL

CONTACT POINT	3	Cu Sn	1
CONTACT POINT	2	Cu Sn	1
PEN HOUSING	1	PBTP GV	GREEN
DESCRIPTION	POS.	MATERIAL	SURFACE COLOR

TE Connectivity. All Rights Reserved.



DIMENSIONS: mm	DWN W.HOFFMANN 16MAY1983	MATERIAL -	FINISH -
	CHK M.Schaarschmidt 17MAY1983	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0.2 mm	APVD -		
0 PLC ± -	PRODUCT SPEC -	NAME AMPMODU II STIFTLEISTE 90 ZWEIREIHIG	
1 PLC ± -	APPLICATION SPEC -		
2 PLC ± -	WEIGHT -	SIZE A4	CAGE CODE 00779
3 PLC ± -		DRAWING NO C-827932	RESTRICTED TO -
4 PLC ± -			
ANGLES ± -			
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1
			REV B1