


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E1	REVISED PER ECN-23-215330	24JUL2023	RK	MF

NOTES:

△1 MIN. 3µm TIN OVER 1.27µm NICKEL

△2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI  
OBSOLETE

POS. PER ROW	L±0.5	PART NUMBER		
-	-	-	-	-
2	5.08	829-262-2	2	△3
3	7.62		3	△3
4	10.16		4	△3
5	12.70		5	△2
6	15.24		6	△3
7	17.78		7	△3
8	20.32		8	△3
9	22.86		9	△3
10	25.40	1	0	△2
11	27.94	1	1	△3
12	30.48	1	2	△2
13	33.02	1	3	△3
14	35.56	1	4	△3
15	38.10	1	5	△2
16	40.64	1	6	△3
17	43.18	1	7	△3
18	45.72	1	8	△3
19	48.26	1	9	△3
20	50.80	2	0	△2
21	53.34	2	-1	
22	55.88	2	-2	
23	58.42	2	-3	
24	60.96	2	-4	
25	63.50	2	-5	
26	66.04	2	-6	
27	68.58	2	-7	
28	71.12	2	-8	
29	73.66	2	-9	
30	76.20	3	0	△3
31	78.74	3	1	△3
32	81.28	3	2	△3
33	83.82	3	3	△3
34	86.36	3	4	△3
35	88.90	3	5	△3
36	91.44	3	6	△3
37	93.98	3	7	△3
38	96.52	3	8	△3
39	99.06	3	9	△3
40	101.60	4	0	△3
41	104.14	4	1	△3
42	106.68	4	2	△3
43	109.22	4	3	△3
44	111.76	4	4	△3
45	114.30	4	5	△3
46	116.84	4	6	△3
47	119.38	4	7	△3
48	121.92	4	8	△3
49	124.46	4	9	△3
50	127.00	5-829-262-0	0	△3



CONTACT PIN	CuZn	△1
PIN HOUSING	PBT	GREEN
DESCRIPTION	MATERIAL	COLOR/ FINISH

TE Connectivity. All Rights Reserved.



DIMENSIONS: mm	DWN	G HOLAUS	17.07.89	MATERIAL	SEE TABLE	FINISH	SEE NOTE 1
	CHK	M SCHAARSCHMIDT	17.07.89	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm	APVD	G FELDMIEIER	12.11.92				
	PRODUCT SPEC	108-18012		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± -	APPLICATION SPEC	-		A4	00779	C-829262	-
1 PLC ± -	WEIGHT	-		CUSTOMER DRAWING			SCALE
2 PLC ± -							4:1
3 PLC ± -							SHEET
4 PLC ± -							1 OF 1
ANGLES ± -							REV
							E1