

1 REVISIONS


P	LTR	2 DESCRIPTION	DATE	DWN	APVD
	A1	PART OBSOLESCENCE	09JUL2024	RS	VG

1 $2.0\mu\text{m}$ min. Zinn über $1.27\mu\text{m}$ Nickel

2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

3 OBSOLETE

POLZ PRO REIHE	L ± 0.4	BESTELL-NR.
—	—	—
2	5.08	— 829 290 — 2 $\triangle 3$
3	7.62	— — 3 $\triangle 3$
4	10.16	— — — 4 $\triangle 3$
5	12.70	— — — 5 $\triangle 3$
6	15.24	— — — 6 $\triangle 3$
7	17.78	— — — 7 $\triangle 3$
8	20.32	— — — 8 $\triangle 3$
9	22.86	— — — 9 $\triangle 3$
10	25.40	1 — — 0 $\triangle 3$
11	27.94	1 — — — 1 $\triangle 3$
12	30.48	1 — — — 2 $\triangle 3$
13	33.02	1 — — — 3 $\triangle 3$
14	35.56	1 — — — 4 $\triangle 3$
15	38.10	1 — — — 5 $\triangle 3$
16	40.64	1 — — — 6 $\triangle 3$
17	43.18	1 — — — 7 $\triangle 3$
18	45.72	1 — — — 8 $\triangle 3$
19	48.26	1 — — — 9 $\triangle 3$
20	50.80	2 — — — 0 $\triangle 3$
21	53.34	2 — — — 1 $\triangle 3$
22	55.88	2 — — — 2 $\triangle 3$
23	58.42	2 — — — 3 $\triangle 3$
24	60.96	2 — — — 4 $\triangle 3$
25	63.50	2 — — — 5 $\triangle 3$
26	66.04	2 — — — 6 $\triangle 3$
27	68.58	2 — — — 7 $\triangle 3$
28	71.12	2 — — — 8 $\triangle 3$
29	73.66	2 — — — 9 $\triangle 3$
30	76.20	3 — — — 0 $\triangle 3$
31	78.74	3 — — — 1 $\triangle 3$
32	81.28	3 — — — 2 $\triangle 3$
33	83.82	3 — — — 3 $\triangle 3$
34	86.36	3 — — — 4 $\triangle 3$
35	88.90	3 — — — 5 $\triangle 3$
36	91.44	3 — — — 6 $\triangle 3$
37	93.98	3 — — — 7 $\triangle 3$
38	96.52	3 — — — 8 $\triangle 3$
39	99.06	3 — — — 9 $\triangle 3$
40	101.60	4 — — — 0 $\triangle 3$
41	104.14	4 — — — 1 $\triangle 3$
42	106.68	4 — — — 2 $\triangle 3$
43	109.22	4 — — — 3 $\triangle 3$
44	111.76	4 — — — 4 $\triangle 3$
45	114.30	4 — — — 5 $\triangle 3$
46	116.84	4 — — — 6 $\triangle 3$
47	119.38	4 — — — 7 $\triangle 3$
48	121.92	4 — — — 8 $\triangle 3$
49	124.46	4 — — — 9 $\triangle 3$
50	127.00	5 — 829 290 — 0 $\triangle 3$




3	CONTACT	CuSn	1 $\triangle 3$
2	CONTACT	CuSn	1 $\triangle 3$
1	HOUSING	PBTP GV	GREEN
POS	DESCRIPTION	MATERIAL	SURFACE/COLOUR

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
 $\pm 0.2 \text{ mm}$

0 PLC	$\pm -$
1 PLC	$\pm -$
2 PLC	$\pm -$
3 PLC	$\pm -$
4 PLC	$\pm -$
ANGLES	$\pm -$



DWN G.HOLAUS 17.07.89

CHK M.SCHAARSCHMIDT

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

MATERIAL

SEE TABLE

FINISH

SEE TABLE

TE

TE Connectivity

NAME

AMPMODU II STIFTLEISTE 90

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4 00779 C-829290

CUSTOMER DRAWING

SCALE

4:1

SHEET

1 OF 1

REV A1

