

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P	PART OBSOLESCENCE	31JUL2024	RS	VG

POS.	L	+0.3 -0.5	PART-NO.
-	-	-	-
2	5.08	826653	-2
3	7.62		3
4	10.16		4
5	12.70		5
6	15.24		-6
7	17.78		-7
8	20.32		-8
9	22.86		-9
10	25.40	1	0
11	27.94	1	1
12	30.48	1	2
13	33.02	1	3
14	35.56	1	4
15	38.10	1	5
16	40.64	1	6
17	43.18	1	7
18	45.72	1	8
19	48.26	1	9
20	50.80	2	0
21	53.34	2	1
22	55.88	2	2
23	58.42	2	3
24	60.96	2	4
25	63.50	2	5
26	66.04	2	6
27	68.58	2	7
28	71.12	2	8
29	73.66	2	9
30	76.20	3	0
31	78.74	3	1
32	81.28	3	2
33	83.82	3	3
34	86.36	3	4
35	88.90	3	5
36	91.44	3	-6
37	93.98	3	7
38	96.52	3	8
39	99.06	3	9
40	101.60	4	0
41	104.14	4	1
42	106.68	4	2
43	109.22	4	3
44	111.76	4	4
45	114.30	4	5
46	116.84	4	6
47	119.38	4	7
48	121.92	4	8
49	124.46	4	9
50	127.00	5- 826653	-0

1 OBSOLETE

SEE DIAGRAM
826629 SHEET 3

OBSOLETE



OBSOLETE



TE Connectivity. All Rights Reserved.

THERE IS NO ORIGINAL OF THIS DRAWING



DIMENSIONS: mm	DWN —	MATERIAL —	FINISH —				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK —	 TE Connectivity					
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	APVD —			PRODUCT SPEC —	NAME AMPMODU II STIFTELEISTE 90		
	APPLICATION SPEC —	SIZE A4	CAGE CODE 00779	DRAWING NO C-826653	RESTRICTED TO —		
	WEIGHT —	CUSTOMER DRAWING			SCALE —	SHEET 1 of 1	REV P