

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P1	PART OBSOLESCENCE	02AUG2024	AR	VG

POS PER ROW	L ± 0.3 -0.5	PART-NO.
2	5.08	826953 -2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6 
7	17.78	-7 
8	20.32	-8
9	22.86	-9
10	25.40	1- -0
11	27.94	1- -1 
12	30.48	1- -2 
13	33.02	1- -3
14	35.56	1- -4 
15	38.10	1- -5 
16	40.64	1- -6 
17	43.18	1- -7 
18	45.72	1- -8 
19	48.26	1- -9 
20	50.80	2- -0 
21	53.34	2- -1 
22	55.88	2- -2 
23	58.42	2- -3 
24	60.96	2- -4 
25	63.50	2- -5 
26	66.04	2- -6 
27	68.58	2- -7 
28	71.12	2- -8 
29	73.66	2- -9 
30	76.20	3- -0 
31	78.74	3- -1 
32	81.28	3- -2
33	83.82	3- -3 
34	86.36	3- -4 
35	88.90	3- -5 
36	91.44	3- -6
37	93.98	3- -7 
38	96.52	3- -8 
39	99.06	3- -9 
40	101.60	4- -0 
41	104.14	4- -1 
42	106.68	4- -2 
43	109.22	4- -3 
44	111.76	4- -4 
45	114.30	4- -5 
46	116.84	4- -6 
47	119.38	4- -7 
48	121.92	4- -8 
49	124.46	4- -9 
50	127.00	5- 826953 -0


 OBSOLETE

SEE DIAGRAM
826629 SHEET 2

TE Connectivity. All Rights Reserved.



THERE IS NO ORIGINAL OF THIS DRAWING

DIMENSIONS: mm	DWN —	—	MATERIAL —	FINISH —	
	CHK —	—	 TE Connectivity		
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD —	—			
	PRODUCT SPEC —	NAME AMPMODU II STIFTLEISTE 90DEG ZWEIREIHIG			
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	APPLICATION SPEC —	SIZE A4	CAGE CODE 00779	DRAWING NO C-826953	RESTRICTED TO —
		WEIGHT —	CUSTOMER DRAWING		
		SCALE —	SHEET 1 of 1		REV P1