


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	PART OBSOLESCENCE	03JUL2024	AR	VG

POLZ. PRO REIHE	L±0.4	BESTELL-NR.		
-	-	-	-	
2	5.08	828	132	2
3	7.62	-	-	3
4	10.16	-	-	4
5	12.70	-	-	5
6	15.24	-	-	6
7	17.78	-	-	7
8	20.32	-	-	8
9	22.86	-	-	9
10	25.40	1	-	0
11	27.94	1	-	1
12	30.48	1	-	2
13	33.02	1	-	3
14	35.56	1	-	4
15	38.10	1	-	5
16	40.64	1	-	6
17	43.18	1	-	7
18	45.72	1	-	8
19	48.26	1	-	9
20	50.80	2	-	0
21	53.34	2	-	1
22	55.88	2	-	2
23	58.42	2	-	3
24	60.96	2	-	4
25	63.50	2	-	5
26	66.04	2	-	6
27	68.58	2	-	7
28	71.12	2	-	8
29	73.66	2	-	9
30	76.20	3	-	0
31	78.74	3	-	1
32	81.28	3	-	2
33	83.82	3	-	3
34	86.36	3	-	4
35	88.90	3	-	5
36	91.44	3	-	6
37	93.98	3	-	7
38	96.52	3	-	8
39	99.06	3	-	9
40	101.60	4	-	0
41	104.14	4	-	1
42	106.68	4	-	2
43	109.22	4	-	3
44	111.76	4	-	4
45	114.30	4	-	5
46	116.84	4	-	6
47	119.38	4	-	7
48	121.92	4	-	8
49	124.46	4	-	9
50	127.00	5	828 132	0



- 1 STECKSEITE: IM BEREICH "F" 0.76µm (PdNi + Au FLASH)
(alternative plating – min 0.76µm au plating)
ÜBER 1.27µm NICKEL
- LÖTSEITE: MIN. 2.5µm ZINN ÜBER 1.27µm NICKEL
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 3 OBSOLETE

KONTAKTSTIFT	Cu Zn	
STIFTGEHÄUSE	PBT GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

TE Connectivity. All Rights Reserved.



DIMENSIONS:		DWN	31.08.89		MATERIAL		-		FINISH		-	
mm		CHK	G.HOLAUS		TE Connectivity							
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm		SCHAAR.										
		APVD										
		-										
PRODUCT SPEC		108-18012		NAME								
APPLICATION SPEC		-		AMPMODU II STIFTLEISTE ZWEIREIHIG								
0 PLC ± -		WEIGHT		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO		
1 PLC ± -				A4		00779		C-828132		-		
2 PLC ± -												
3 PLC ± -												
4 PLC ± -		CUSTOMER DRAWING		SCALE		4:1		SHEET		1 OF 1		
ANGLES ± -		-		REV		C2						
												