





POS. PER ROW	L ±0.5	PART - NO.	POS. PER ROW	L ±0.5	PART - NO.
-	-	-	26	66.04	2-829-394-6 ²
2	5.08	829-394-2 ³	27	68.58	2- ⁷ ²
3	7.62	³	28	71.12	2- ⁸ ²
4	10.16	⁴	29	73.66	2- ⁹ ²
5	12.70	⁵	30	76.20	3- ⁰ ²
6	15.24	6 ³	31	78.74	3- ¹ ²
7	17.78	⁷	32	81.28	3- ²
8	20.32	⁸	33	83.82	3- ³ ²
9	22.86	9 ³	34	86.36	3- ⁴ ²
10	25.40	1-	35	88.90	3- ⁵ ²
11	27.94	1 ²	36	91.44	3- ⁶ ²
12	30.48	1 ²	37	93.98	3- ⁷ ³
13	33.02	1 ³	38	96.52	3- ⁸ ³
14	35.56	1 ²	39	99.06	3- ⁹ ³
15	38.10	1 ³	40	101.60	4- ⁰ ³
16	40.64	1 ²	41	104.14	4- ¹ ³
17	43.18	1-	42	106.68	4- ² ³
18	45.72	1 ²	43	109.22	4- ³ ³
19	48.26	1 ²	44	111.76	4- ⁴ ³
20	50.80	2- ³	45	114.30	4- ⁵ ³
21	53.34	2- ³	46	116.84	4- ⁶ ³
22	55.88	2- ²	47	119.38	4- ⁷ ³
23	58.42	2- ²	48	121.92	4- ⁸ ³
24	60.96	2- ²	49	124.46	4- ⁹ ³
25	63.50	2-829-394-5 ³	50	127.00	5-829-394-0 ³

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	CONTACT PIN MATERIAL AND PLATING CHANGE	16OCT2014	KJK	JK
	B1	NOTE 1 0.76 µm PLATING UPDATE (PdNi+AuFLASH)	14JUL2023	BGC	PS
	B	PART OBSOLESCENCE	19DEC2024	RS	VG



- 1 MIN 0.76 µm (PdNi + Au FLASH) BY AREA "F" OVER MIN, 1.27 µm Ni BY AREA "B" IN AREA "C" MIN. 3 µm TIN OVER MIN. 1.27 µm Ni (Alternative plating - Min 0.76 µm Au OVER 1.27 µm Ni)
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 3 OBSOLETE

1	CuZn	CONTACT PIN KONTAKTSTIFT
COLOUR GREEN	PBT GV UL 94 - V0	PIN HOUSING STIFTGEHAEUSE
REMARK BEMERKUNG	MATERIAL	DESCRIPTION BEZEICHNUNG



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24 JUN2005 G.ACKERMANN	TE Connectivity		
DIMENSIONS: mm		CHK 24 JUN2005 M.SCHAARSCHMIDT			
		APVD 24 JUN2005 G.FELDMEIER			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
0 PLC ±0.2		108-18012	NAME AMPMODU II PIN HEADER, DUAL ROW		
1 PLC ±0.2		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
2 PLC ±0.2		-	A3 00779 C-829394		
3 PLC ±		WEIGHT -	SCALE 5:1 SHEET 1 OF 1 REV B2		
4 PLC ±		CUSTOMER DRAWING			
ANGLES ±2°					
FINISH -					