


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—						
NUMMER	829 092		1	CAD-NEUERSTELLUNG	31.08.89	—	G.HOLAUS
VERWENDET FÜR	E87-9277		2	REVISED PER ECO-09-024717	11NOV09	—	AEG
WAR NR.	7-87-9277-0 9-87-9277-0		3	ECR-10-025774	24JAN11	KK	HMR

POLZ-PRO REIHE	L±0.4	BESTELL-NR.
—	—	—
2	5.08	-2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	-8
9	22.86	-9
10	25.40	1-
11	27.94	1-
12	30.48	1-
13	33.02	1-
14	35.56	1-
15	38.10	1-
16	40.64	1-
17	43.18	1-
18	45.72	1-
19	48.26	1-
20	50.80	2-829 092-0
21	53.34	2-
22	55.88	2-
23	58.42	2-
24	60.96	2-
25	63.50	2-
26	66.04	2-
27	68.58	2-
28	71.12	2-
29	73.66	2-
30	76.20	3-
31	78.74	3-
32	81.28	3-
33	83.82	3-
34	86.36	3-
35	88.90	3-
36	91.44	3-
37	93.98	3-
38	96.52	3-
39	99.06	3-
40	101.60	4-829 092-0
41	104.14	4-
42	106.68	4-
43	109.22	4-
44	111.76	4-
45	114.30	4-
46	116.84	4-
47	119.38	4-
48	121.92	4-
49	124.46	4-
50	127.00	5-



- ① STECKSEITE: IM BEREICH "F" 0.4 μm GOLD ÜBER 1.27 μm NICKEL
LÖTSEITE: MIN. 2.5 μm ZINN ÜBER 1.27 μm NICKEL
- ② OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- ③ OBSOLETE

CAD-ORIGINAL ZEICHNUNG NICHT ÄNDERN		
KONTAKTSTIFT	Cu Sn	①
STIFTGEHÄUSE	PBTP-GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

ZEICHNUNG GÜLTIG AB 35/89.....

THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. RELEASED FOR PUBLICATION.

DIMENSIONS: mm	DWN	31.08.89	MATERIAL	—	FINISH	—
	CHK	—	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	25.02.92				
±0.2 mm	PRODUCT SPEC	—	NAME			
0 PLC ± -	APPLICATION SPEC	—	AMPMODU II STIFTLAISTE ZWEIREIHIG			
1 PLC ± -	WEIGHT	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2 PLC ± -			A4	00779	C-829092	—
3 PLC ± -			CUSTOMER DRAWING			
4 PLC ± -			SCALE	SHEET	REV	
ANGLES ± -			4:1	1 OF 1	3	