

D

C

B

A

PART NO.	A	B	C	D	E	F	REMARKS
849103-1	24.00 [609.6]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	—	⚠ OBSOLETE
849103-2	15.00 [381.0]	1.00 [25.4]	.50 [12.7]	6.00 [152.4]	2.00 [50.8]	—	⚠ OBSOLETE
849103-3	30.00 [762.0]	4.00 [101.6]	.38 [9.7]	6.00 [152.4]	3.00 [76.2]	6.00 [152.4]	⚠ OBSOLETE
849103-4	8.00 [203.2]	1.00 [25.4]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	—	⚠ OBSOLETE
849103-5	18.00 [457.2]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
849103-6	48.00 [1219.2]	2.00 [50.8]	—	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
849103-7	11.00 [279.4]	1.50 [38.1]	.38 [9.7]	—	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
849103-8	96.00 [2438.4]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
849103-9	120.00 [3048.0]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
1-849103-0	20.00 [508.0]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
1-849103-1	60.00 [1524.0]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
1-849103-2	46.00 [1168.4]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
1-849103-3	155.00 [3937.0]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
1-849103-4	480.00 [12192.0]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
1-849103-5	12.50 [317.5]	1.00 [25.4]	.50 [12.7]	10.00 [254.0]	3.00 [76.2]	—	⚠ OBSOLETE
1-849103-6	312.00 [7924.8]	2.00 [50.8]	.50 [12.7]	6.00 [152.4]	3.00 [76.2]	—	⚠ OBSOLETE
1-849103-7	84.00 [2133.6]	12.00 [304.8]	.38 [9.7]	6.00 [152.4]	3.00 [76.2]	6.00 [152.4]	⚠ OBSOLETE
1-849103-8	27.00 [685.8]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
1-849103-9	48.00 [1219.2]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
2-849103-0	72.00 [1828.8]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
2-849103-1	480.00 [12192.0]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	—	⚠ OBSOLETE
2-849103-2	8.00 [203.2]	1.00 [25.4]	.38 [9.7]	—	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
2-849103-3	240.00 [6096.0]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
2-849103-4	20.50 [520.7]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
2-849103-5	108.00 [2743.2]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
5-849103-5	18.00 [457.2]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
5-849103-6	48.00 [1219.2]	2.00 [50.8]	—	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE
5-849103-8	96.00 [2438.4]	2.00 [50.8]	.38 [9.7]	6.00 [152.4]	2.00 [50.8]	6.00 [152.4]	⚠ OBSOLETE


- 1TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
- 2MARKED PER MIL-STD-130.
- 3TO MATE WITH TE LGH-1
RECEPTACLE WITH .88 [22.4] BARREL DEPTH.
- 4OPERATING VOLTAGE: 25 KVDC AT 0 TO 70,000 FEET,
-55°C TO 125°C.
- 5PIGTAILS ARE SOLDER DIPPED.
- 6INSULATION CUT, BUT NOT REMOVED.

D

C

B

A



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 05-NOV-93		TE Connectivity	
DIMENSIONS: INCHES [mm]		CHK S.GLATFELTER 22-NOV-93		NAME	
		RPVD S.GLATFELTER 22-NOV-93		PRODUCT SPEC	
		APPLICATION SPEC		SIZE	
		WEIGHT 0.000000		A100779	
MATERIAL SEE CALLOUTS		FINISH		CUSTOMER DRAWING	
		SCALE 2:1		SHEET 1 OF 1	