



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E2	PART OBSOLESCENCE	14AUG2024	KA	PS

NOTES:

△1 MIN. 3μm TIN OVER 1.27μm NICKEL

△2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI
△3 OBSOLETE

POS. PER ROW	L±0.5	PART NUMBER	
—	—	—	—
2	5.08	— 829 262 2	△3
3	7.62	— 3	△3
4	10.16	— 4	△3
5	12.70	— 5	△2
6	15.24	— 6	△3
7	17.78	— 7	△3
8	20.32	— 8	△3
9	22.86	— 9	△3
10	25.40	1 0	△2
11	27.94	1 1	△3
12	30.48	1 2	△2
13	33.02	1 3	△3
14	35.56	1 4	△3
15	38.10	1 5	△2
16	40.64	1 6	△3
17	43.18	1 7	△3
18	45.72	1 8	△3
19	48.26	1 9	△3
20	50.80	2 0	△2
21	53.34	2 1	△3
22	55.88	2 2	△3
23	58.42	2 3	△3
24	60.96	2 4	△3
25	63.50	2 5	△3
26	66.04	2 6	△3
27	68.58	2 7	△3
28	71.12	2 8	△3
29	73.66	2 9	△3
30	76.20	3 0	△3
31	78.74	3 1	△3
32	81.28	3 2	△3
33	83.82	3 3	△3
34	86.36	3 4	△3
35	88.90	3 5	△3
36	91.44	3 6	△3
37	93.98	3 7	△3
38	96.52	3 8	△3
39	99.06	3 9	△3
40	101.60	4 0	△3
41	104.14	4 1	△3
42	106.68	4 2	△3
43	109.22	4 3	△3
44	111.76	4 4	△3
45	114.30	4 5	△3
46	116.84	4 6	△3
47	119.38	4 7	△3
48	121.92	4 8	△3
49	124.46	4 9	△3
50	127.00	5 829 262 0	△3



CONTACT PIN	CuZn	△1
PIN HOUSING	PBT	GREEN
DESCRIPTION	MATERIAL	COLOR/ FINISH

TE Connectivity. All Rights Reserved.



DIMENSIONS: mm	DWN G HOLAUS 17.07.89	MATERIAL SEE TABLE	FINISH SEE NOTE 1
	CHK M SCHAARSCHMIDT 17.07.89	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm	APVD G FELDMEIER 12.11.92		
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC 108-18012	NAME SPECIAL AMPMODU II PIN HEADER DUAL ROW	
	APPLICATION SPEC —	SIZE A4	CAGE CODE 00779
	WEIGHT —	DRAWING NO C-829262	RESTRICTED TO —
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1
		REV E2	