


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C3	PART OBSOLESCENCE	01AUG2024	AR	VG

POS.	L±0.4	PART NO.
-	-	-
2	5.08	— —2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	829487 -7
8	20.32	-8
9	22.86	829487 -9
10	25.40	1- -0
11	27.94	1- -1
12	30.48	1- -2
13	33.02	1- -3
14	35.56	1- -4
15	38.10	1- -5
16	40.64	1- -6
17	43.18	1- -7
18	45.72	1- -8
19	48.26	1- -9
20	50.80	2- -0
21	53.34	2- -1
22	55.88	2- -2
23	58.42	2- -3
24	60.96	2- -4
25	63.50	2- -5
26	66.04	2- -6
27	68.58	2- -7
28	71.12	2- -8
29	73.66	2- -9
30	76.20	3- -0
31	78.74	3- -1
32	81.28	3- -2
33	83.82	3- -3
34	86.36	3- -4
35	88.90	3- -5
36	91.44	3- -6
37	93.98	3- -7
38	96.52	3- -8
39	99.06	3- -9
40	101.60	4- -0
41	104.14	4- -1
42	106.68	4- -2
43	109.22	4- -3
44	111.76	4- -4
45	114.30	4- -5
46	116.84	4- -6
47	119.38	4- -7
48	121.92	4- -8
49	124.46	4- -9
50	127.00	5- -0



CONTACT PIN	CuZn	⚠
HOUSING	PBT	GREEN
DESCRIPTION	MATERIAL	FINISH/COLOR

⚠ MATING SIDE: Min 0.76µm (PdNi + Au FLASH) IN ZONE "F" OVER Min 1.27µm Ni
(Alternative plating – Min 0.76µm Au OVER Min 1.27µm Ni)
SOLDER SIDE: 3.0 TO 5.0µm TIN OVER 1.27µm NICKEL.

⚠ OBSOLETE

TE Connectivity. All Rights Reserved.



DIMENSIONS: mm		DWN A.HO	21FEB1990	MATERIAL -	FINISH -
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm		CHK M.SCHAARSCHMIDT	-	 TE Connectivity	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD -	-		
		PRODUCT SPEC 108-18012		NAME AMPMODU II BREAK AWAY HEADER, SINGLE ROW	
		APPLICATION SPEC -		SIZE A4	CAGE CODE 00779
		WEIGHT -		DRAWING NO C-829487	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1
				REV C2	