



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L1	REVISED PER ECO-09-020932	08SEP09	KK	AEG
	M	REVISED PER ECO-18-000976	13APR2018	RS	JO



- 1 CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF .125 TOLERANCES NON-CUMULATIVE.
- 2 USE EXTRACTION TOOL 91052-2 TO REMOVE RECEPTACLE CONTACTS.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECT X-X

		OBSOLETE	1.610	.750	.750	13	1-86402-7
		OBSOLETE	1.360	.625	.625	11	1-86402-6
		OBSOLETE	3.485	1.625	1.750	28	1-86402-5
SUPERSEDED BY	1-86401-4		.735	.250	.375	6	1-86402-4
		OBSOLETE	2.985	1.375	1.500	24	1-86402-3
		OBSOLETE	2.235	1.000	1.125	18	1-86402-2
		OBSOLETE	2.110	.875	1.125	17	1-86402-1
		OBSOLETE	1.985	.875	1.000	16	1-86402-0
	△3	OBSOLETE	.360	.125	.125	3	86402-9
SUPERSEDED BY	86401-8		1.235	.500	.625	10	86402-8
		OBSOLETE	1.735	.750	.875	14	86402-7
	△3	OBSOLETE	.610	.250	.250	5	86402-6
			.235	.125	—	2	86402-5
			1.485	.625	.750	12	86402-4
		OBSOLETE	.985	.375	.500	8	86402-3
		OBSOLETE	.485	.125	.250	4	86402-2
			2.485	1.125	1.250	20	86402-1
			C	B	A	NO OF POS	PART NUMBER (MARKED)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14SEP89 BOB BOLES BG CHK 23OCT89 J. GESFORD APVD 23OCT89 J. GESFORD PRODUCT SPEC — APPLICATION SPEC —		 TE Connectivity Ltd.	
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
INCHES		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± 0°30'		CONNECTOR, CRIMP SNAP-IN, MOD IV, SINGLE ROW, .125 CENTERS.	
		FINISH		SIZE	CAGE CODE
MATERIAL		WEIGHT		DRAWING NO	
GLASS FILLED NYLON COLOR—BLACK		—		A2	—
		CUSTOMER DRAWING		C-86402	RESTRICTED TO
				SCALE	SHEET
				4:1	1 of 1
				REV	M