



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F3	PART REACTIVATION	24JAN2025	KS	PS

POS. "n"	L±0.4	PART NO.
2	4.58	829539 -2
3	7.12	829539 -3
4	9.66	829539 -4
5	12.20	829539 -5
6	14.74	829539 -6
8	19.82	829539 -8
48	121.42 -0.5	4-829539-8
50	126.50 -0.5	5-829539-0



NOTES:

- 1

MATING SIDE: Min 0.76µm (PdNi + Au FLASH)IN ZONE "F" OVER Min 1.27µm Ni
(Alternative plating - Min 0.76µm Au OVER Min 1.27µm Ni)
SOLDER SIDE: MIN. 3.0µm TIN OVER Min 1.27µm NICKEL
- 2

OBSOLETE

2	CONTACT PIN KONTAKTSTIFT	CuZn	1
1	PIN HOUSING STIFTGEHÄUSE	PA 4/6	BLACK SCHWARZ
POS.	BENENNUNG EINZELTEIL	WERKSTOFF	OBERFLÄCHE
[ITEM NO.]	[DESCRIPTION]	[MATERIAL]	FARBE
			[FINISH]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MULLER	09FEB1990	TE Connectivity		
		CHK SCHAARSCHMIDT	12FEB1990			
DIMENSIONS: mm		APVD —	—	NAME AMPMODU II PIN HEADER, SINGLE ROW		
		PRODUCT SPEC 108-18012	—			
		APPLICATION SPEC —	—			
MATERIAL SEE TABLE		WEIGHT —	—	SIZE A3	CAGE CODE 00779	DRAWING NO C-829539
FINISH SEE TABLE		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV F3