


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
DF	S0	P	LTR	DESCRIPTION	DATE	DWN	APVD
		G		REV PER ECO 05-015021	27JAN06	BL	CT



- 1 TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
- 2. MARKED PER MIL-STD-130.
- 3. TO MATE WITH AMP LGH-1/2 RECEPTACLE WITH .53 [13.4] BARREL DEPTH.
- 4 WHERE APPLICABLE "B" STRIP LENGTH IS SOLDER DIPPED.
- 5. OPERATING VOLTAGE: 10 KVDC AT 0 TO 70,000 FEET, -55° C TO 125° C.
- 6 INSULATION CUT, BUT NOT REMOVED.

	6	5-893898-2	.38 [9.7]	24.00 [508.0]	5-867945-2
	4	893898-2	.38 [9.7]	24.00 [508.0]	867945-2
OBSOLETE	4	893898-1	.38 [9.7]	10.00 [254.0]	867945-1
REMARKS		CUSTOMER PART NO.	B	A 1	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	C.C.THOMAS	1-5-90	Tyco Electronics Corporation Harrisburg, PA 17105-3608
DIMENSIONS: INCHES		CHK	D.EABY	4-27-90	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	-	-	NAME
0 PLC ± -		PRODUCT SPEC	-	-	LEAD ASS'Y, SGL. MOLDED END, LGH-1/2
1 PLC ± -		APPLICATION SPEC	-	-	SIZE
2 PLC ± .02 [0.5]		WEIGHT	-	-	CAGE CODE
3 PLC ± -		CUSTOMER DRAWING	-	-	DRAWING NO
4 PLC ± -		SCALE	4:1	-	RESTRICTED TO
ANGLES ± -		SHEET	1 of 1	-	REV
FINISH -		REV	G	-	