



© COPYRIGHT

REVISIONS		DATE	APPROVED
P	ZONE LTR	DESCRIPTION	
	J1	REVISED PER ECN-23-225110	08AUG 2023
			RK MF



POST NOS (REF ONLY)

- 1. TRUE POSITION TOLERANCE OF POST TIPS APPLIES WHEN HEADERS ARE HELD FLAT AGAINST PRINTED CIRCUIT BOARD.
- 2. POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3. .00015 GOLD ON CONTACT AREA GOLD FLASH ON SOLDER AREA ALL OVER .00050 NICKEL.
- 4. OBSOLETE PART NUMBER
- 5. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



1,2,3,4	3.984	3.900	39	40	4-87465-2	
1	3.984	3.900	39	40	4-87465-1	
NONE	3.884	3.800	38	39	4-87465-0	
	3.784	3.700	37	38	3-4	
	3.684	3.600	36	37	3-4	
	3.584	3.500	35	36	3-4	
	3.484	3.400	34	35	3-4	
	3.384	3.300	33	34	3-4	
	3.284	3.200	32	33	3-4	
	3.184	3.100	31	32	3-4	
	3.084	3.000	30	31	3-4	
	2.984	2.900	29	30	3-4	
	2.884	2.800	28	29	3-4	
	2.784	2.700	27	28	2-4	
	2.684	2.600	26	27	2-4	
	2.584	2.500	25	26	2-4	
	2.484	2.400	24	25	2-4	
	2.384	2.300	23	24	2-4	
	2.284	2.200	22	23	2-4	
	2.184	2.100	21	22	2-4	
	2.084	2.000	20	21	2-4	
	1.984	1.900	19	20	2-4	
	1.884	1.800	18	19	2-4	
	1.784	1.700	17	18	1-4	
	1.684	1.600	16	17	1-4	
	1.584	1.500	15	16	1-4	
	1.484	1.400	14	15	1-4	
	1.384	1.300	13	14	1-4	
	1.284	1.200	12	13	1-4	
	1.184	1.100	11	12	1-4	
	1.084	1.000	10	11	1-4	
	.984	.900	9	10	1-4	
	.884	.800	8	9	1-4	
	.684	.600	6	7	1-4	
	.584	.500	5	6	1-4	
	.484	.400	4	5	1-4	
	.384	.300	3	4	1-4	
	.284	.200	2	3	1-4	
	.184	.100	1	2	1-4	
	.084	—	—	1	1-4	
	3.984	3.900	39	40	87465-2	
	NONE	.784	.700	7	8	87465-1
	NONE	C	IB	IA	NO. OF POSTS	PART NO

5 OBSOLETE  
5 OBSOLETE  
5 OBSOLETE

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.005 ANGLES ±	CONTRACT NO	<b>STE</b> TE Connectivity	
	DR: <i>BA Wolfe</i> 11-7-72		
MATERIAL HSG.: LCP COLOR: BLACK	CHK: <i>Dillworth</i> 5-28-75	NAME HEADER ASSY, MOD II, .025 SQ. POSTS, SINGLE ROW, .100 CENTERS	
FINISH: POSTS: 5	APPD: <i>Bennett</i> 5/30/75	SIZE	CODE IDENT NO
	APPD: <i>R. Clark</i> 5/30/75	C	00779
	DSGN APPD	DRAWING NO	87465
	OTHER APPD	SCALE	SHEET
		REV	J1