

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L1	REVISED PER ECN-22-171534	30AUG2022	RK	JO

- 1

PLATING IS NOT REQUIRED IN THIS AREA.
- 2

CUT-OUTS ON BOX AT MANUFACTURER'S OPTION.
- 3

.006 MAX LOOSE PIECE CUT-OFF.
- 4

POINT OF MEASUREMENT FOR PLATING THICKNESS(INSIDE BEAMS).
- 5

.000015 GOLD IN CONTACT AREA, GOLD FLASH ON REMAINDER OF TERMINAL, ALL OVER .000050 NICKEL.
- 6

.000030 GOLD OVER .000050 NICKEL.
- 7

.000030 GOLD IN CONTACT AREA, GOLD FLASH ON REMAINDER OF TERMINAL, ALL OVER .000050 NICKEL.
- 8

PREPLATED: .000078-.000158 BRIGHT TIN.
- 9







.000030 GOLD IN CONTACT AREA, GOLD FLASH IN AREA L, ALL OVER .000050 NICKEL.
- 10

.000050 GOLD IN CONTACT AREA, GOLD FLASH ON REMAINDER OF TERMINAL, ALL OVER .000050 NICKEL.
- 11

SHEARED EDGES PERMITTED TO BE UNPLATED.
- 12

OBSOLETE PART NUMBER.
- 13

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



OBSOLETE OBSOLETE	12 -6	1-	12 -7	10	1 =86492=8
	12 -5	1-	12 -4	9	1 =-3
	87046-4		12 -8	8	-9
	12 -3		12 -5	7	-6
	12 -2		12 -3	6	-4
	87046-1		12 -1	5	86492-2
	LOOSE PIECE PART NUMBER		STANDARD APPLICATOR PART NUMBER	FINISH	MINI APPLICATOR PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L A MAYER 20MAY85	TE Connectivity	
		CHK R J DAVIS 07JUN85		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C LINDGREN 14JUN85	NAME	
	0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± .005 4. PLC ± - ANGLES ± - ± -	PRODUCT SPEC	CONTACT, MOD IV 1/2, RECEPTACLE, CRIMP SNAP-IN	
	FINISH -	APPLICATION SPEC	-	
MATERIAL CU-NI-SI		WEIGHT -	SIZE A1	CAGE CODE 00779
		DRAWING NO 86492	RESTRICTED TO	
		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1
			REV L1	