



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	W	REVISED PER ECR-22-137476	23AUG2022	RK	SD
	W1	REVISED PER ECN-23-211206	24JUN2023	RK	MF
	W2	NOTE 9 AND 10 REMOVED	22FEB2025	VP	PS
	W3	NOTE UPDATION,PRODUCT & APPLICATION SPEC ADDED	14APR2025	RS	GVF

SUPRSEDED BY 3-87499-4			-	45.72	20.32	22.86	18	8-87499-9	
SUPRSEDED BY 3-87499-2			-	43.18	20.32	20.32	17	8-87499-8	
SUPRSEDED BY 3-87499-0			-	40.64	17.78	20.32	16	8-87499-7	
SUPRSEDED BY 2-87499-8			-	38.10	17.78	17.78	15	8-87499-6	
SUPRSEDED BY 2-87499-6			-	35.56	15.24	17.78	14	8-87499-5	
SUPRSEDED BY 2-87499-4			-	33.02	15.24	15.24	13	8-87499-4	
SUPRSEDED BY 2-87499-2			-	30.48	12.70	15.24	12	8-87499-3	
SUPRSEDED BY 2-87499-0			-	27.94	12.70	12.70	11	8-87499-2	
SUPRSEDED BY 1-87499-8			-	25.40	10.16	12.70	10	8-87499-1	
SUPRSEDED BY 1-87499-6			-	22.86	10.16	10.16	9	8-87499-0	
	OBSOLETE		-	20.32	7.62	10.16	8	7-87499-9	
SUPRSEDED BY 87499-2			-	17.78	7.62	7.62	7	7-87499-8	
SUPRSEDED BY 1-87499-2			-	15.24	5.08	7.62	6	7-87499-7	
SUPRSEDED BY 1-87499-0			-	12.70	5.08	5.08	5	7-87499-6	
SUPRSEDED BY 87499-8			-	10.16	2.54	5.08	4	7-87499-5	
SUPRSEDED BY 87499-6			-	7.62	2.54	2.54	3	7-87499-4	
SUPRSEDED BY 87499-4			-	5.08	-	2.54	2	7-87499-3	
		-	-	2.54	-	-	1	7-87499-2	
SUPRSEDED BY 7-87499-2		-	ALL	2.54	-	-	1	7-87499-1	
	OBSOLETE	-	-	91.44	43.18	45.72	36	7-87499-0	
	OBSOLETE	-	ALL	91.44	43.18	45.72	36	6-87499-9	
	OBSOLETE	-	-	88.90	43.18	43.18	35	6-87499-8	
	OBSOLETE	-	ALL	88.90	43.18	43.18	35	6-87499-7	
	OBSOLETE	-	-	86.36	40.64	43.18	34	6-87499-6	
	OBSOLETE	-	ALL	86.36	40.64	43.18	34	6-87499-5	
	OBSOLETE	-	-	83.82	40.64	40.64	33	6-87499-4	
	OBSOLETE	-	ALL	83.82	40.64	40.64	33	6-87499-3	
	OBSOLETE	-	-	81.28	38.10	40.64	32	6-87499-2	
	OBSOLETE	-	ALL	81.28	38.10	40.64	32	6-87499-1	
	OBSOLETE	-	-	78.74	38.10	38.10	31	6-87499-0	
	OBSOLETE	-	ALL	78.74	38.10	38.10	31	5-87499-9	
		-	-	76.20	35.56	38.10	30	5-87499-8	
		-	ALL	76.20	35.56	38.10	30	5-87499-7	
		-	-	73.66	35.56	35.56	29	5-87499-6	
		-	ALL	73.66	35.56	35.56	29	5-87499-5	
		-	-	71.12	33.02	35.56	28	5-87499-4	
		-	ALL	71.12	33.02	35.56	28	5-87499-3	
		-	-	68.58	33.02	33.02	27	5-87499-2	
		-	ALL	68.58	33.02	33.02	27	5-87499-1	
		-	-	66.04	30.48	33.02	26	5-87499-0	
		-	ALL	66.04	30.48	33.02	26	4-87499-9	
		-	-	63.50	30.48	30.48	25	4-87499-8	
		-	ALL	63.50	30.48	30.48	25	4-87499-7	
		-	-	60.96	27.94	30.48	24	4-87499-6	
			NOTES	MARKING	L	B	A	NO OF POSN	PART NUMBER




-	ALL	60.96	27.94	30.48	24	4-87499-5
-	-	58.42	27.94	27.94	23	4-87499-4
-	ALL	58.42	27.94	27.94	23	4-87499-3
-	-	55.88	25.40	27.94	22	4-87499-2
-	ALL	55.88	25.40	27.94	22	4-87499-1
-	-	53.34	25.40	25.40	21	4-87499-0
-	ALL	53.34	25.40	25.40	21	3-87499-9
-	-	50.80	22.86	25.40	20	3-87499-8
-	ALL	50.80	22.86	25.40	20	3-87499-7
	-	48.26	22.86	22.86	19	3-87499-6
-	ALL	48.26	22.86	22.86	19	3-87499-5
-	-	45.72	20.32	22.86	18	3-87499-4
-	ALL	45.72	20.32	22.86	18	3-87499-3
-	-	43.18	20.32	20.32	17	3-87499-2
-	ALL	43.18	20.32	20.32	17	3-87499-1
-	-	40.64	17.78	20.32	16	3-87499-0
-	ALL	40.64	17.78	20.32	16	2-87499-9
-	-	38.10	17.78	17.78	15	2-87499-8
-	ALL	38.10	17.78	17.78	15	2-87499-7
-	-	35.56	15.24	17.78	14	2-87499-6
-	ALL	35.56	15.24	17.78	14	2-87499-5
-	-	33.02	15.24	15.24	13	2-87499-4
-	ALL	33.02	15.24	15.24	13	2-87499-3
-	-	30.48	12.70	15.24	12	2-87499-2
-	ALL	30.48	12.70	15.24	12	2-87499-1
-	-	27.94	12.70	12.70	11	2-87499-0
-	ALL	27.94	12.70	12.70	11	1-87499-9
-	-	25.40	10.16	12.70	10	1-87499-8
-	ALL	25.40	10.16	12.70	10	1-87499-7
-	-	22.86	10.16	10.16	9	1-87499-6
-	ALL	22.86	10.16	10.16	9	1-87499-5
-	-	20.32	7.62	10.16	8	1-87499-4
-	ALL	20.32	7.62	10.16	8	1-87499-3
-	-	15.24	5.08	7.62	6	1-87499-2
-	ALL	15.24	5.08	7.62	6	1-87499-1
-	-	12.70	5.08	5.08	5	1-87499-0
-	ALL	12.70	5.08	5.08	5	87499-9
-	-	10.16	2.54	5.08	4	87499-8
-	ALL	10.16	2.54	5.08	4	87499-7
-	-	7.62	2.54	2.54	3	87499-6
-	ALL	7.62	2.54	2.54	3	87499-5
-	-	5.08	-	2.54	2	87499-4
-	ALL	5.08	-	2.54	2	87499-3
-	-	17.78	7.62	7.62	7	87499-2
-	ALL	17.78	7.62	7.62	7	87499-1
NOTES	MARKING	L	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. BRANDBERG CHK S. SHUEY APVD D. DUPLER	21-JUN-95 21-JUN-95 21-JUN-95	 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.13 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH -		NAME HOUSING, MOD IV, SINGLE ROW, .100 CL, CRIMP SNAP-IN		RESTRICTED TO	
		PRODUCT SPEC 108-25020		SIZE A2		CAGE CODE 00779	
MATERIAL - 		APPLICATION SPEC 114-25003, 114-25016		DRAWING NO C-87499		REV. W3	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 2	

NAME				
HOUSING, MOD IV, SINGLE ROW, .100 CL, CRIMP SNAP-IN -				
SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO
A2	00779	C-87499		-
		SCALE	SHEET	REV
		4:1	2 OF 2	W3



- SECTION Y - Y



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN F. BRANDBERG 21-JUN-95		 TE Connectivity	
		CHK S. SHUEY 21-JUN-95			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HOUSING, MOD IV, SINGLE ROW, .100 CL, CRIMP SNAP-IN	
		0 PLC ±- 1 PLC ±- 2 PLC ±0.13 3 PLC ±- 4 PLC ±- ANGLES ±-			
MATERIAL		FINISH		RESTRICTED TO	
		-		-	
CUSTOMER DRAWING				SIZE A2	CAGE CODE 00779
				DRAWING NO C-87499	
				SCALE 4:1	SHEET 2 OF 2
				REV W3	