




NOTE:


- 1 SEE TABLE FOR NUMBER OF DETENTS. DETENT ON THIS SIDE FOR HOUSINGS WITH ONE DETENT.
- 2 STRAIN RELIEF LOCATORS WILL APPEAR ON 20 POSITION AND LARGER HOUSINGS
- 3 USE EXTRACTION TOOL 843996-3 TO REMOVE RECEPTACLE CONTACTS
- 4 THESE HOUSINGS ARE COMPATIBLE WITH ANY MOD II SHROUDED HEADER
- 5 HOUSINGS WILL ACCOMMODATE ALL MOD IV, IV.5, AND MOD V CONTACTS.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 7 MATERIAL: LCP, UL 94-V0 RATED, COLOR: BLACK.
- 10 CRITICAL DIMENSION: MAX. FLASH PERMITTED OF 0.127 [0.005] mm EITHER SIDE.
- 11 PART NO., AND DATE CODE IS MARKED IN AREA AS SHOWN WHEN HOUSING SIZE PERMITS (SEE TABLE).
- 12 NO PART NUMBER AND DATE CODE MARKING MAY BE ROTATED 90 deg




LONGEST POSITION SHOWN




SECTION X-X




ISOMETRIC VIEW



3-87631-0
SCALE 2:1



87631-8
SCALE 2:1



ALL	6-87631-5	2	81.28 [3.2]	31	64	6-87631-6
ALL	6-87631-3	2	73.66 [2.9]	28	58	6-87631-4
ALL	6-87631-1	2	71.12 [2.8]	27	56	6-87631-2
ALL	5-87631-9	2	60.96 [2.4]	23	48	6-87631-0
ALL	5-87631-7	2	91.44 [3.6]	35	72	5-87631-8
ALL	5-87631-5	2	88.9 [3.5]	34	70	5-87631-6
ALL	5-87631-3	2	83.82 [3.3]	32	66	5-87631-4
ALL	5-87631-1	2	76.2 [3.0]	29	60	5-87631-2
ALL	4-87631-9	2	-	-	-	5-87631-0
ALL	4-87631-7	2	-	-	-	4-87631-8
ALL	4-87631-5	2	68.58 [2.7]	26	54	4-87631-6
ALL	4-87631-3	2	66.04 [2.6]	25	52	4-87631-4
ALL	4-87631-1	2	63.5 [2.5]	24	50	4-87631-2
ALL	3-87631-9	2	55.88 [2.2]	21	44	4-87631-0
ALL	3-87631-7	2	53.34 [2.1]	20	42	3-87631-8
ALL	3-87631-5	2	50.8 [2.0]	19	40	3-87631-6
ALL	3-87631-3	2	48.26 [1.9]	18	38	3-87631-4
ALL	3-87631-1	2	45.72 [1.8]	17	36	3-87631-2
ALL	2-87631-9	2	43.18 [1.7]	16	34	3-87631-0
ALL	2-87631-7	2	40.64 [1.6]	15	32	2-87631-8
ALL	2-87631-5	2	38.1 [1.5]	14	30	2-87631-6
ALL	2-87631-3	2	35.56 [1.4]	13	28	2-87631-4
ALL	2-87631-1	2	33.02 [1.3]	12	26	2-87631-2
ALL	1-87631-9	2	30.48 [1.2]	11	24	2-87631-0
ALL	1-87631-7	2	27.94 [1.1]	10	22	1-87631-8
ALL	1-87631-5	2	25.4 [1.0]	9	20	1-87631-6
ALL	1-87631-3	1	22.86 [0.9]	8	18	1-87631-4
ALL	1-87631-1	1	20.32 [0.8]	7	16	1-87631-2
ALL	87631-9	1	17.78 [0.7]	6	14	1-87631-0
ALL	87631-7	1	15.24 [0.6]	5	12	87631-8
NO PART #	87631-5	1	12.7 [0.5]	4	10	87631-6
NO PART #	87631-3	1	10.16 [0.4]	3	8	87631-4
	87631-1	1	7.62 [0.3]	2	6	87631-2
MARKING	UNMARKED HOUSING PART NUMBER	NUMBER OF DETENTS	"L" DIM	"A" NUMBER OF SPACES	NUMBER OF POSITIONS	MARKED HOUSING PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09FEB94 E BRANDENBERG CHK 08NOV94 S SHUEY APVD 08NOV94		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 P/LC ±.010 1 P/LC ±.010 2 P/LC ±.010 (0.019) 3 P/LC ±.010 (0.131) [0.019] 4 P/LC ±.010 ANGLES ±0° 30' FINISH		NAME MOD IV CRIMP SNAP-IN CONNECTOR, DOUBLE ROW, 2.54 [0.10] CENTERS SHORT ENTRY SIZE CAGE CODE DRAWING NO RESTRICTED TO A 00779 C-87631 -	
		APPLICATION SPEC 114-25003, 114-25016 WEIGHT -		SCALE 5:1 SHEET 1 OF 1 REV AB	
MATERIAL		CUSTOMER DRAWING			
					