



DO NOT SCALE
DIMENSIONS IN mm


METRIC




3rd ANGLE PROJECTION



SECÇÃO A-A



SECÇÃO B-B



OBSOLETE

ACCORDING EC LB00-0140-01

NOTAS:

- 1 - FLASH DE OURO NA ÁREA "X", ESTANHO NA ÁREA DE CRIMPAGEM SOBRE 1,27µm DE NÍQUEL.
- 2 - 0,38 µm OURO NA ÁREA "X", ESTANHO NA ÁREA DE CRIMPAGEM SOBRE 1,27µm DE NÍQUEL EM TODO O CONTATO.
- 3 - 0,76 µm OURO NA ÁREA "X", ESTANHO NA ÁREA DE CRIMPAGEM SOBRE 1,27µm DE NÍQUEL EM TODO O CONTATO.
- 4 - MATERIAL: LATÃO

↑	- 3	3	↑	↑	↑	↑	↑	↑	- 3
↑	- 2	2	↑	↑	↑	↑	↑	↑	- 2
880 187 - 1	1	24-28 AWG	1,5	1,4	2,0	2,4	880 216 - 1		
↑	- 3	3	↑	↑	↑	↑	↑	↑	- 3
↑	- 2	2	↑	↑	↑	↑	↑	↑	- 2
880 186 - 1	1	20-24 AWG	1,9	1,7	2,0	2,4	880 215 - 1		
STRIP FORM P.N.	FINISH	WIRE RANGE	D	C	B	A	L. P. NUMBER		
CUSTOMER DWG for REFERENCE ONLY			THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION © COPYRIGHT 19 BY AMP DO BRASIL LTDA S.P. ALL INTERNATIONAL RIGHTS RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.						
			TOLERANCES UNLESS OTHERWISE STATED DEC. ± 0,5 ANGLES ± 1°		INS. DIA. RANGE WIRE RANGE SCALE		AMP do BRASIL LTDA. São Paulo, Brasil		
			DR. <i>Donato</i> 27/7/83						
			CHK. <i>TAA</i> 28-7-83		DESCRIPTION CONTACT, PIN HD-20 (LOOSE PIECE)				
			DE. <i>28-01-91</i>						
B REVISADO EC LB-0140-01 HC. <i>10 Apr 01</i>			APP. <i>28-7-83</i>		DWG NO 880 215 C 880 216				
A Revisado notas 1-2-3 <i>10 Apr 01</i>			APP. <i>28-7-83</i>		SHEET 1 of 1				
O ERAP-8329206/207 <i>28-7-83</i>			APP. <i>28-7-83</i>						
ISS	REVISION	RECORD	DR	CHK	DATE	APP. <i>28-7-83</i>			