



NOTE:


1. CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF 2.54 [0.1] TOLERANCES ARE NON-CUMULATIVE.
2. USE EXTRACTION TOOL 843996-3 TO REMOVE RECEPTACLE CONTACTS
3. THESE HOUSINGS ARE COMPATIBLE WITH ANY MOD II SHROUDED HEADER
4. HOUSINGS WILL ACCOMMODATE ALL MOD IV, IV.5, AND MOD V CONTACTS.
5. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
6. PART NO., AND DATE CODE IS MARKED IN AREA AS SHOWN WHEN HOUSING SIZE PERMITS (SEE TABLE).
7. CAVITY IDENTS ON SECOND AND EVERY FIFTH CAVITY IS MARKED ON ONE SIDE AS SHOWN.
8. STRAIN RELIEF LOCATORS WILL APPEAR ON 20 POSITION AND LARGER HOUSINGS.
9. MATERIAL: GLASS FILLED THERMOPLASTIC, UL 94-V0 RATED, COLOR: BLACK.
10. NO PART NUMBER AND DATE CODE MARKING MAY BE ROTATED 90 deg




LONGEST POSITION SHOWN




ISOMETRIC VIEW



87977-4 & 3-87977-1
SCALE 2:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 18DEC89		TE Connectivity	
DIMENSIONS:		MOD BOLES BG P. SREMICCH 050CT93 P. SREMICCH 050CT93			
mm [INCHES]		NAME MOD IV CRIMP SNAP-IN CONNECTOR, DOUBLE ROW, 2.54 [0.1] CENTERS		TE Connectivity	
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 1 P/LC ± 2 P/LC ±0.5 [0.02] 3 P/LC ±0.13 [0.005] 4 P/LC ± ANGLES ±0° 30' FINISH		PRODUCT SPEC 108-25020 APPLICATION SPEC 114-25003, 114-25016	
MATERIAL		WEIGHT		RESTRICTED TO	
		A 00779		C=87977	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1 REV. W	