


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A5	REVISED PER ECN-25-313588	31MAR2025	WLS	RE





1 REELING WITH PAPER INTERLEAVE.


2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINIG PER D.RENAUD / D.SINISI.

3 WIRE RANGE : 0,5-1,0mm².

4 INSULATION RANGE : Ø 2,0 - 3,3 mm.





SECTION A - A



SECTION B - B

2	OBSOLETE	TIN PLATED	BRASS	880626-4
2	OBSOLETE	—	PHOS. BRONZE	880626-3
		TIN PLATED	BRASS	880626-2
		—	BRASS	880626-1
		FINISH	MATERIAL	PART NO



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W. STEFANI 20MAR2025		 TE Connectivity				
		CHK RAGHAVENDRA E. 02APR2025						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0,4 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±1°		NAME				
				RING TONG				
MATERIAL SEE TABLE				SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
				A3		-	C-880626	-
		APVD W. MOYER 02APR2025						
		PRODUCT SPEC						
		-						
		APPLICATION SPEC						
		-						
		WEIGHT						
		-						
		CUSTOMER DRAWING						
				SCALE	3:1	SHEET 1 OF 1	REV A5	