





P	LTR	DESCRIPTION	DATE	DWN	APVD
	B5	REV. BY ECO 17-017464	28NOV2017	HC	PK
	C	REVISED PER ECN-25-307751	20MAR2025	WLS	RE



- 1 REELING WITH PAPER INTERLEAVE.
- 2 WIRE RANGE : >1,0 - 2,5 mm2.
- 3 INSULATION RANGE : Ø 2,7 - 4,0 mm.





SECTION A - A



SECTION B - B

OBSOLETE	TIN PLATED	BRASS	880643-6
OBSOLETE	NICKEL PLATED	BRASS	880643-5
OBSOLETE	TIN PLATED	PHOSP. BRONZE	880643-4
OBSOLETE		PHOSP. BRONZE	880643-3
	TIN PLATED	BRASS	880643-2
		BRASS	880643-1
	FINISH	MATERIAL	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NCLAPRESA 10DEC2014	 TE Connectivity		
DIMENSIONS: mm		CHK FFORTUNATO 10DEC2014			
		APVD LWPRADO 10DEC2014			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
0 PLC ± 1 PLC ±0,3 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1°		APPLICATION SPEC	RING TONG		
MATERIAL SEE TABLE		FINISH SEE TABLE	SIZE A3	CAGE CODE -	DRAWING NO C-880643
		WEIGHT -	RESTRICTED TO -		
CUSTOMER DRAWING			SCALE 3:1	SHEET 1 OF 1	REV C