

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.





© COPYRIGHT -

LOC

DIST



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
F		DOVE TAIL ADDED / Schwalbenschwanz eingefuegt	27JUL2006	C.H.	C.G.
G		DRAWING ADAPTED / Zeichnung angepasst	13AUG2007	Abr	C.G.
H		SPOT WELDING CHANGED INTO LINE WELDING	27SEP2012	Sch	Abr


NOTES
Bemerkungen

- 1 1-3 μm Sn
1-3 μm Sn
- 2 3-4 μm GALVANIC Ag
REST GALV. Sn (1-3 μm)
3-4 μm galvanisch Ag
Rest galv. Sn (1-3 μm)
- 3 WIRE RANGE
Drahtgroessenbereich (mm²): 0.5-1
- 4 INSULATION RANGE FOR SWS Ø6 (mm): 1.4-2.0
Isolationsbereich fuer EDS Ø6

Teilansicht A




OPTIONAL



vorversilbert	0-962952-2	H
vorverzinnt	0-962952-1	H
FINISH	PART NO.	REV.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±	±0.2mm
1 PLC	±	±0.2mm
2 PLC	±	±0.2mm
3 PLC	±	±0.2mm
4 PLC	±	±0.2mm
ANGLES	±	±1.5°
FINISH	-	-

MATERIAL
CuNiSi

DWN

E. Palmie

02FEB1995

CHK

H. Lutsch

02FEB1995

APVD

PRODUCT SPEC

108-18472

APPLICATION SPEC

114-18118

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

Ø4mm SOCKET CONTACT, SWS
Ø4mm Buchsenkontakt, EDS

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-962952

RESTRICTED TO

-

SCALE 5:1

SHEET

1 OF 1

REV H