

© 2019 TE Connectivity. All Rights Reserved.

POS.	L±0.8	PART NUMBER
2	5.08	925369-2
3	7.62	925369-3
4	10.16	925369-4
5	12.70	925369-5
6	15.24	925369-6
7	17.78	925369-7
8	20.32	925369-8
9	22.86	925369-9
10	25.40	1-925369-0
11	27.94	1-925369-1
12	30.48	1-925369-2
13	33.02	1-925369-3
14	35.56	1-925369-4
15	38.10	1-925369-5
16	40.64	1-925369-6
17	43.18	1-925369-7
18	45.72	1-925369-8
19	48.26	1-925369-9
20	50.80	2-925369-0
21	53.34	2-925369-1
22	55.88	2-925369-2
23	58.42	2-925369-3
24	60.96	2-925369-4
25	63.50	2-925369-5
26	66.04	2-925369-6
27	68.58	2-925369-7
28	71.12	2-925369-8
29	73.66	2-925369-9
30	76.20	3-925369-0
31	78.74	3-925369-1
32	81.28	3-925369-2
33	83.82	3-925369-3
34	86.36	3-925369-4
35	88.90	3-925369-5
36	91.44	3-925369-6
37	93.98	3-925369-7
38	96.52	3-925369-8
39	99.06	3-925369-9
40	101.60	4-925369-0
41	104.14	4-925369-1
42	106.68	4-925369-2
43	109.22	4-925369-3
44	111.76	4-925369-4
45	114.30	4-925369-5
46	116.84	4-925369-6
47	119.38	4-925369-7
48	121.92	4-925369-8
49	124.46	4-925369-9
50	127.00	5-925369-0

OBSOLETE

POS.X2.54 = L±0.8

2.54

1

14.2

2.94

2.5

2

VIEW A

SCALE 3:1

PN 1-925369-0 FROM DIFFERENT CAVITIES AS SHOWN BELOW

POSITIONS OF LOCKING CHANGED CONDITIONAL OF PRODUCTION KNUPS LOCK ACCORDING ON THE LEFT OR RIGHT SIDE WITH PIN HEADER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

FINISH

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±0.2mm

±
±
±
±
±
±

-
-

MATERIAL
PA66
GREEN RAL 6001

DWN
KARTHIK J K
CHK
HARI REDDY
APVD
PRASHANTH S
PRODUCT SPEC

28AUG2019
28AUG2019
28AUG2019

3

APPLICATION SPEC
114-25003

WEIGHT
-

CUSTOMER DRAWING

TE

TE Connectivity

NAME
AMPMODU IV RECEPTACLE HOUSING
SINGLE ROW , WITH STRAIN RELIEF
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-925369

RESTRICTED TO
-

SCALE
5:1

SHEET
1 OF 1

REV
Y1

1471-9 (3/13)