





LOC AL DIST 2

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	J6	REVISED PER ECR-18-010208	23JUL2018	BDA	SF




NOTES:

Bemerkungen:

- 1 2-6µm Sn OVER Ni IN CRIMP-AREA
2-6µm Sn über Ni in der Crimpzone
- 2 0.8µm Au OVER Ni IN CONTACT-AREA
0.8µm Au über Ni in der Kontaktzone
- 3 SUITABLE FOR Ø1.0-2.5mm
Für Isolations Ø1.0-2.5mm geeignet
- 4 0.8µm Au OVER 1.3µm Ni ON INSIDE OF WIRE BARREL AND CONTACT AREA
0.8µm Au über 1.3µm Ni in der Drahtcrimp und Kontaktzonen, sonst 1.3µm Ni

SUPERSEDED BY 350851-7	926895-7	926884-7	BRASS	1 2
SUPERSEDED BY 350851-7	926895-6	926884-6	PHOS BRONZE	1 2
	926895-3	926884-3	PHOS BRONZE	PRE-TIN
OBSOLETE	926895-2	926884-2	BRASS	4
	926895-1	926884-1	BRASS	PRE-TIN
	LOOSE PIECE	PART NO.	MATERIAL	FINISH



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. Skoda 07NOV2005	STE TE Connectivity		
DIMENSIONS: mm		CHK R. Vlcek			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME UNIVERSAL MNL SOCKET 0.2-0.8 mm ² WIRE RANGE		
0 PLC ±0.2		PRODUCT SPEC 108-1031			
1 PLC ±0.2		APPLICATION SPEC 114-18011	SIZE A3	CAGE CODE 00779	DRAWING NO C-926884
2 PLC ±0.2		WEIGHT -	RESTRICTED TO		
3 PLC ±		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1	REV J6
4 PLC ±					
ANGLES ±°					
FINISH SEE TABLE					