





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	OWN	APVD
A1	-		F1	Zeichnung wird NEUTRAL	31JUL1996	Beu	-
			F2	Material bleifrei	13SEP2004	Stein	-
			F3	Bem. 2 korrigiert	26AUG2005	Beu	-
			F4	New drawing created / note 3 updated	11MAR2008	Haas	Zitz



- 7 APPLICATION TOOL; X-Y- MACHINE 2-872 020-9
Verarbeitungswerkzeug; X-Y-Einsetzmaschine 2-872 020-9
- 6 1-2 μm TIN IN AREA "F" ABOVE
1.2 μm NICKEL IN AREA "L"
AREA "C": 5.0 μm TIN ABOVE 1.2 μm NICKEL
1-2 μm Zinn im Bereich "F" über
1.2 μm Nickel im Bereich "L"
Im Bereich "C" 5.0 μm Zinn über 1.2 μm Nickel
- 5 TE-SPEC. 108-18002
TE-Spez.
- 4 SOLDERABILITY ACC. TO DIN40046
Lötbarkeit nach
- 3 REEL UNIT 50000 PINS Rolleneinheit 50000 Stifte
REEL- $\varnothing$ 600MM Rollen- $\varnothing$ 600mm
REEL THICKNESS Rollendicke
- | | |
|---------------------|---|
| 14mm for 1-929958-1 |  |
| 14mm for 2-929958-1 | |
| 19mm for 1-929958-2 | |
| 16mm for 2-929958-2 | |
- 2 PRESS-IN ZONE FOR 1.6mm PCB
REQUIREMENTS ON THE PCB-hole:
Einpresszone für 1.6mm Leiterplatte
Anforderung an Leiterplatten-Bohrung:
- Bohrlochdurchmesser / HOLE DIAMETER: $1.0 \pm 0.025\text{mm}$
Cu-Dicke / Cu-THICKNESS: 25-50 μm
Sn-Dicke / Sn-THICKNESS: 4-10 μm
Fertiglochdurchmesser / FINISHED HOLE DIAMETER: $0.9 \pm 0.05\text{mm}$
- 1 0.2 μm Au IN AREA "F" ABOVE
1.2 μm NICKEL IN AREA "L".
IN AREA "C": 5.0 μm TIN ABOVE
1.2 μm NICKEL.
0.2 μm Au im Bereich "F" über
1.2 μm Nickel im Bereich "L"
Im Bereich "C" 5.0 μm Zinn über
1.2 μm Nickel



NOT FOR NEW APPLICATIONS
Nicht für Neuanwendungen

	CuSn4/F65	7	7	13.2	10	2-929 958-2
	CuSn4/F65	7	6	13.2	10	1-929 958-2
	CuSn4/F65	6.7	6.7	11.45	8.25	2-929 958-1
	CuSn4/F65	6.7	6	11.45	8.25	1-929 958-1
FINISH	MATERIAL	"A"	"F"	"N"	"L"	ORDER NO Bestell-Nr. 
		DIMENSIONS				

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 14 JUL 1989 Zwarnig		Tyco Electronics AMP GmbH 64625 Bensheim (Germany)	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± ±0.2 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±5°		NAME ACTION PIN FOR MICRO QUADLOK SYSTEM -	
		PRODUCT SPEC -		SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-929958 -	
MATERIAL FINISH SSEE TABLE SEE TABLE		APPLICATION SPEC - WEIGHT -		SCALE 5:1 SHEET 1 OF 1 REV F4	
CUSTOMER DRAWING					