CHEMINAX

95 OHM, AWG 30, 7 STRANDS OF AWG 38, COAXIAL CABLE

Date:

04-26-00

Revision:

Α

THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200.

CONSTRUCTION DETAILS

DIMENSIONS ARE NOMINAL VALUES IN INCHES UNLESS OTHERWISE DESIGNATED

CONDUCTOR AWG 30, 7 Strands of .0127 AWG 38, Tin-Coated Copper Covered Steel DIELECTRIC .080 Rayfoam® L Color - Natural SHIELD .097 AWG 38. Tin-Coated Copper **JACKET** 117 Thermorad® S

Outer jacket color will be black, designated by a "0" appended to the part number (e.g., 9530A1317-0), unless otherwise specified.

Designate outer jacket color with a dash number in accordance with MIL-STD-681.

ELECTRICAL CHARACTERISTICS

CHARACTERISTIC IMPEDANCE

95 ± 5 ohms, Method B

CAPACITANCE

13.5 pF/ft. (nominal) at 1 kHz

VELOCITY OF PROPAGATION

79% (nominal)

ADDITIONAL REQUIREMENTS

ELECTRICAL

CONDUCTORRESISTANCE **INSULATION RESISTANCE**

255. ohms/1000 ft. (nominal)

10,000 megohms (minimum) for 1000 ft.

JACKET FLAWS

SPARK TEST **IMPULSE TEST**

1.0 kV (rms) 6.0 kV (peak)

VOLTAGE WITHSTAND

1000 volts (rms), (minimum)

(DIELECTRIC)

ENVIRONMENTAL

FLAMMABILITY HEAT SHOCK

Method C 225°C

LOWTEMPERATURE-**COLD BEND**

-55°C/3.25 inch mandrel

VOLTAGE WITHSTAND (POST ENVIRONMENTAL)

1000 volts (rms), 1 minute

PHYSICAL

INSULATION (DIELECTRIC)

ELONGATION TENSILE STRENGTH

50% (minimum)

800 lbf/in2 (minimum)

JACKET

ELONGATION TENSILE STRENGTH 250% (minimum) 2000 lbf/in2 (minimum)

JACKET THICKNESS SHIELD COVERAGE

.010 inch (nominal)

90% (minimum)

WEIGHT

8.2 lbs/1000 ft. (nominal)

Raychem