

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	PN 1-964106-1 OBSOLETE	07OCT14	PKS	RRP
	A4	REVISED PER ECR-24-226209	06DEC2024	PS	TD

D

D

C


C

B

B


A

A



- △1 Kontakt geeignet fuer:
Lackdraht Ø0.6-0.80mm
(Einzeldraht oder zwei Draehte gleichen Durchmessers)
Slot accepts:
SINGLE MAGNET WIRE Ø0.6-0.80mm
DOUBLE MAGNET WIRE SAME DIAMETERS
- △2 Flachstecker A2.8-0.5mm oder A2.8-0.8mm nach DIN 46244
FLAT PIN A2.8-0.5mm OR A2.8-0.8mm ACCORDING TO DIN 46244
- △3 Bereich wird beim Kontaktieren abgetrennt
AREA WILL BE CUTTED OF BY TERMINATION
- △4 Kontakt Kammer nach Zeichnung 411-18514
CAVITY ACCORDING DWG 411-18514
- △5 Kennziffer fuer Lackdrahtbereich (12)
IDENTIFICATION NO. (12)
- △6 Unter Vorstrich-Zahl 1-...
auch "ohne" Rastnase lieferbar
UNDER PRAEFIX NO: 1-
ALSO "WITHOUT LOCKING NOSE AVAILABEL

1-964106-2 △6	A	-	MAG-MATE Kontakt "without"	CuNiSi	POSTTINNED
1-964106-1 △6	A	-	MAG-MATE Kontakt "without"	CuNiSi	PRETINNED
964106-2	A	-	MAG-MATE Kontakt "with"	CuNiSi	POSTTINNED
964106-1	A	-	MAG-MATE Kontakt "with"	CuNiSi	PRETINNED
COSTUMER PART NO	REV	PCS	DESCRIPTION	MATERIAL	SURFACE COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.Holch	10-02-92	TE Connectivity			
		CHK H.PL	10-02-92				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm		APVD -	NAME MAG-MATE TERMINAL WITH TAB-RECEPT. 2.8-0.5/0.8 -			
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1°		PRODUCT SPEC -				
			APPLICATION SPEC -				
	MATERIAL SEE TABLE -		FINISH SEE TABLE -	WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-964106
Customer Drawing				SCALE 10:1	SHEET 1 OF 1	REV A4	