


ATUM (4: | RATIO)

DUAL WALL TUBE.WITH A 4:1 SHRINK RATIO. A HALOGENATED FLAME RETARDED HEAT SHRINK TUBE WITH A MELTABLE ADHESIVE LINER DELIVERING A HIGH BOND STRENGTH TO MANY SUBSTRATES. TO BE USED FOR INSULATION, PROTECTION, AND ENVIRONMENTAL SEALING OF CABLES.



PRODUCT DIMENSIONS

TOTAL WALL THICKNESS INNER MELTABLE WALL INSIDE DIAMETER AS INSIDE DIAMETER WALL THICKNESS THICKNESS AFTER AFTER RECOVERY SI7F TOLERANCE AFTER SUPPLIED (MIN) AFTER RECOVERY (MAX) (NOM) RECOVERY (NOM) \bigcap RECOVERY d WI mm. in. mm. in. mm. in. mm. in. mm. in. 4.00 . 157 .039 0.30 .012 0.50 4/1 1.00 .039 1.00 .020 .315 .039 0.30 .012 0.50 .020 8/2 8.00 2.00 .079 1.00 . 055 .024 12/3 12.00 . 472 3.00 . 118 1.40 0.30 .012 0.60 16/4 16.00 .630 4.00 . 157 1.78 .070 0.38 .015 0.75 .030 24/6 24.00 . 945 6.00 . 236 2.25 .089 0.55 .022 0.80 .031 32/8 32.00 1.260 . 3 | 5 2.54 0.55 .022 .039 8.00 . 100 1.00 52/13 52.00 2.047 13.00 . 5 | 2 2.54 0.55 .022 039 . 100 1.00

ATUM (4: | RATIO)

PRODUCT INFORMATION

SHRINK RATIO - 4:1 LONGITUDINAL SHRINKAGE ON FULL RECOVERY 0 TO -15% MATERIAL CONFORMS TO TE SPECIFICATION 108-120009

STANDARD COLOUR: BLACK FLAME RETARDANT

TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING.

STANDARD CUTTING TOLERANCES(mm)		TILLO DRAWLING 10 A 6	20NTDOLLED DOCUMENT	DWN 0.7DEC.2022			
CUT LENGTH	TOLERANCE	HIS DRAWING IS A C	CONTROLLED DOCUMENT.	BASAVARAJA D A	STE	TE Connectivit	у
UPTO TO 9.90mm	\pm 1.50mm	DIMENSIONS:	TOLERANCES UNLESS	SELVAPANDIAN B APVD 07DEC2022			
10mm TO 24.90mm	\pm 1.50mm	mm (Inches)	OTHERWISE SPECIFIED.	MAYO BAKARE PRODUCT SPEC	\downarrow AIUM (4:1) RAI	IO-IRRADIATED MO	
25mm TO 54.90mm	\pm 1.50mm		0 PLC ±-	108-120009	1	_ WALL HEAT SHR	INK
55mm TO 99.90mm	± 3.00 mm		2 PLC ±0.01 3 PLC ±0.001	APPLICATION SPEC	TUBING		
100mm TO 149.90mm	\pm 4.00mm		4 PCC ±0.0001 ANGLES ±-	-	SIZE CAGE CODE DRAWING NO		RESTRICTED TO
150mm TO 499.90mm	± 5.00 mm	MATERIAL SEE NOTE	FINISH -	WEIGHT _	A 3 - G-AIUM_4_	to_RATIO_STANDARD_SIZES	-
500mm AND GREATER	±25.40mm	-	-	CUSTOMER DRAWING	sc	ALE NTS SHEET OF	REV A 2

1470-19 (3/13)

В