


NUMMER	966573
VERWENDET FÜR	E 93-52 660
WAR NR.	93-52660-302 BIS -350

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A4	PART OBSOLESCENCE	09JUL2024	AR	VG

POLZ.	L±0.5	BESTELL-NR.
-	-	-
2	5.08	966573 -2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	-8
9	22.86	-9
10	25.40	-0
11	27.94	-1
12	30.48	-2
13	33.02	-3
14	35.56	-4
15	38.10	-5
16	40.64	-6
17	43.18	-7
18	45.72	-8
19	48.26	-9
20	50.80	-0
21	53.34	-1
22	55.88	-2
23	58.42	-3
24	60.96	-4
25	63.50	-5
26	66.04	-6
27	68.58	-7
28	71.12	-8
29	73.66	-9
30	76.20	-0
31	78.74	-1
32	81.28	-2
33	83.82	-3
34	86.36	-4
35	88.90	-5
36	91.44	-6
37	93.98	-7
38	96.52	-8
39	99.06	-9
40	101.60	-0
41	104.14	-1
42	106.68	-2
43	109.22	-3
44	111.76	-4
45	114.30	-5
46	116.84	-6
47	119.38	-7
48	121.92	-8
49	124.46	-9
50	127.00	-0

LOCHBILD DER LEITERPLATE (SICHT AUF LÖTSEITE)
M2.5:1


4 OBSOLETE

3 OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISIGEBOHRTES LOCH 1.0 ±0.025 mm
Cu DICKE 25-50 μm2 Sn/Pb DICKE min. 4 μm
FERTIGE BOHRUNG 0.9 ±0.07mm

1 MIN. 2.0 μm ZINN ÜBER 1.27 μm NICKEL

KONTAKTSTIFT	Cu Sn	1
STIFTGEHÄUSE	PBTP GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

ZEICHNUNG GÜLTIG AB KW 50/94

DIMENSIONS:		DWN	01.06.94		MATERIAL	-		FINISH	-				
mm		CHK	01.06.94		TE Connectivity								
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2 mm		M.SCHAARSCHMIDT		APVD							-		
0 PLC ± -		PRODUCT SPEC		NAME AMPMODU II ACTION STIFTLISTE EINREIHIG									
1 PLC ± -		-											
2 PLC ± -		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
3 PLC ± -		-		A4		00779		C-966573					
4 PLC ± -		GRÜN											
ANGLES ± -		WEIGHT		-									
		CUSTOMER DRAWING				SCALE		4:1		SHEET	1 of 1	REV	A4