



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	NOTE 1 0.76µm PLATING UPDATE (PdNi+AuFLASH)	12JUL2023	BGC	PS

GEGENSTECKER/KONTAKT: ☒


MATED WITH: ☐

1-215297-4 -

POS.	-0.2 -0.6	PART-NO	
6	15.24	0-966764-6	
-	-	-	
-	-	-	
-	-	-	
-	-	-	
14	35.56	1-966764-4	OBSOLETE
-	-	-	



RECOMMENDED PCB LAYOUT





MATING SIDE: Min 0.76µm (PdNi + Au FLASH)IN ZONE "F" OVER Min 1.27µm Ni
(Alternative plating – Min 0.76µm Au by area "F" over Min 1.27µm Nickel)
SOLDER SIDE: MIN. 3.0 TO 5.0 µm TIN OVER 1.27µm NICKLE

CONTACT	CuZn	
HOUSING	PCT-GF	BLACK
DESCRIPTION	MATERIAL	COLOR/FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.HO 28JUL1995	TE Connectivity Ltd.		
		CHK M.SCHAARSCHMIDT 28JUL1995			
		APVD -	NAME		
		PRODUCT SPEC -	AMPMODU II PIN HEADER,SMD SINGLE ROW, BLISTER PACKED		
		APPLICATION SPEC -			
		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-966764
		CUSTOMER DRAWING			RESTRICTED TO -
		SCALE 4:1		SHEET 1 OF 2	REV D2


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



BEMERKUNGEN:

- 1 SIEHE BLATT 1/2
- 2 VERPACKUNGSEINHEIT: 900 STÜCK STIFTLISTEN PN 966 764-6
- 3 ABWICKELRICHTUNG
- 4. VERPACKUNG ENTSPRECHEND DIN/IEC 286 BZW. EIA 481 INKLUSIVE ANGABEN ÜBER DEN VOR- UND NACHLAUF (DIN/IEC 286 TEIL 3)
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

5-966764-6	2	AMPMODU II STIFTLISTE SMD, 6 POL. PN 966764-6	1	1
	1	BLISTERGURT M. ABDECKBAND	PS	GREY/TRANSP.
PART NUMBER	POS.	DESCRIPTION	MATERIAL	COLOR/FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MAHNKE,B.	11SEP2001	 TE Connectivity Ltd.	
		CHK ZITZ,A.	11SEP2001		
		APVD BLEICHER,M.	05NOV2001		
		PRODUCT SPEC			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		AMPMODU II PIN HEADER SMD SINGLE ROW, BLISTER PACKED	
MATERIAL		FINISH		SIZE	RESTRICTED TO
-		-		CAGE CODE	
				DRAWING NO	
				WEIGHT	
				A300779	
				C-966764	
				SCALE	
				1:2	
				SHEET	
				2 OF 2	
				REV	
				D2	