


CUSTOMER DRAWING



Product Names	Product Dimensions			Cable Dimensions		
	L max	A min	K min	D max	F	M±0.5 (M±0.02)
B-801-56-26	17.5 (0.690)	2.5 (0.100)	100 (3.940)	2.5 (0.100)	0.5 (0.020) to 1.4 (0.055)	4 (0.160)


MATERIAL

1. INSULATION SLEEVE: Heat-shrinkable, radiation cross-linked modified polyvinylidene fluoride. Transparent blue.
2. SOLDER PREFORM WITH FLUX:
SOLDER: TYPE Sn63 per ANSI J-STD-006.
FLUX: TYPE ROL0 per ANSI J-STD-004.
3. MELTABLE RING: Thermally stabilized thermoplastic. Color: red.
4. CONDUCTOR LEAD: MIL-W-81822/13 AWG26 solid silver plated copper. Color: white. Quantity: 2.


APPLICATION

1. These parts are designed to terminate a tin or silver plated wire having an insulation rated for at least 125°C with 2 solid wires.
2. Temperature range: -55°C to +150°C.
3. Install using TE Connectivity-approved convection or infrared heating tools in accordance with Raychem installation procedure RPIP-825-00.

For best results, prepare the wire(s) as shown:



TE Connectivity, TE connectivity (logo), Raychem, Thermofit, and SolderSleeve are trademarks

		Raychem THERMOFIT DEVICES		TITLE: SOLDERSLEEVE DEVICE EXTENSION	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE IN BETWEEN BRACKETS.				DOCUMENT NO.: B-801-56-26	
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A		ANGLES: N/A ROUGHNESS IN MICRON		TE Connectivity reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.	
DRAWN BY: R. MAPALO		DATE: 4-Nov-98		Revision: 2	
ECO: ECO-20-003568		SCALE: NONE		Issue Date: March 2020	
SIZE: A		SHEET: 1 of 1			

Print Date: 13-Mar-20 If this document is printed it becomes uncontrolled. Check for the latest revision.