



P	LTR	DESCRIPTION	DATE	DWN	APVD
2		ECR-12-010780	14JUN2012	HD	CD
3		ECR-18-006884	04MAY2018	RS	CD
A		REDRAWN PER ECR-22-157063	02NOV2022	KW	MB



PRODUCT DIMENSIONS & NOTES

DIMENSIONS IN mm(inch)

D DIA.		d DIA.		W	
MIN		MAX		±0.36(.014)	
a		b		b	
mm.	in.	mm.	in.	mm.	in.
19.00	.748	4.00	.157	1.78	.070


LONGITUDINAL SHRINKAGE ON FULL RECOVERY=-10 TO -30%
 SUPPLIED WALL THICKNESS CONCENTRICITY=50% MINIMUM.

MATERIAL: 1. JACKET IRRADIATED MODIFIED POLYOLEFIN
 2. LINER HOT MELT ADHESIVE.

STANDARD CUTTING TOLERANCES(mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm (Inches)



TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC ±.
 1 PLC ±0.1
 2 PLC ±0.01
 3 PLC ±0.001
 4 PLC ±0.0001
 ANGLES ±
 FINISH -

MATERIAL
SEE NOTE

DWN	31OCT2022
BASAVARAJA D A	
CHK	31OCT2022
SELVAPANDIAN B	
APVD	31OCT2022
MAYO BAKARE	
PRODUCT SPEC	108-120009
APPLICATION SPEC	-
WEIGHT	32.70g/m
CUSTOMER DRAWING	



NAME		ATUM-19/4-0	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	©-ATUM-19-4-0	-
SCALE		SHEET	REV
NTS		1 OF 1	A