


DRAWING NO FSLD1410-1430-5-C
THIS DRAWING IS A CONTROLLED DOCUMENT



CATALOGUE NUMBER: FSLD1410-1430-5
SUITS CONDUCTOR

DEADEND

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
6/4.75 + 7/1.60	ACSR	14.30	RIGHT HAND
6/0.186 + 7/0.062	ACSR	14.17	RIGHT HAND
7/4.75	AAC/AAAC	14.25	RIGHT HAND



TECHNICAL SPECIFICATIONS;

CATALOGUE NUMBER: FSLD1410-1430-5
DESCRIPTION: FULL-TENSION SPECIFIC APPLICATION
AL-CLAD STEEL DEADEND
MATERIAL: ALUMINIUM CLAD STEEL WIRE
NUMBER OF RODS: 3
ROD DIAMETER: 4.06mm
OVERAL LENGTH: 1090mm
END FINISH: CHAMFERED
FITTING LAY DIRECTION: RIGHT HAND
COLOUR CODED: BLUE

BOX LABEL

P/N: FSLD1410-1430-5
ID:
DESCRIPTION:
FULL-TENSION AL-CLAD STEEL DEADEND
6/4.75 + 7/1.60 ACSR
6/0.186 + 7/0.062 ACSR
7/4.75 AAC/AAAC
RANGE: 14.10 - 14.30
COLOUR-CODE: BLUE
QTY: 20 WEIGHT: BATCH:

PRODUCT LABEL

FSLD1410-1430-5
6/4.75 + 7/1.60 ACSR
6/0.186 + 7/0.062 ACSR
7/4.75 AAC/AAAC

WEIGHT: 0.75kg
BATCH NO:
MONTH/YEAR:

LOC	DIST	POS	REV	REVISION RECORD	DATE	DWN	APVD	MATERIAL NO	MATL SPEC/STD/DRG NO	PROCESS SPEC HEAT TREAT/PLATING NO	SIZE	PROJECTION	SCALE	DRAWING NO	SHEET	OF	REV
														FSLD1410-1430-5-C	1	1	1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.

D
C
B
A