
## **CUSTOMER DRAWING**



Product		Prod	uct Dimens	sions		Cable Dimensions				
Name	øΑ	øΒ	øС	L	K	øD	øΕ	øF	G±0.5	M±0.5
	min	min	min	max	min			min	(G±0.020)	(M±0.020)
B-026-26-02	6.30	4.60	2.80	36.0	150	2.40	2.30	0.30	19.0	
	(0.250)	(0.180)	(0.110)	(1.415)	(5.900)	(0.095)	(0.090)	(0.012)	(0.750)	6.0
						to	to			(0.235)
						6.30	4.6			
						(0.250)	(0.180)			

## **MATERIALS**

- 1. INSULATION SLEEVE: Heat-shrinkable, radiation cross-linked modified polyolefin. Transparent clear.
- 2. SOLDER PREFORMS WITH FLUX:

SOLDER: Cd18 per ANSI J-STD-006.


FLUX: TYPE ROL0 per ANSI J-STD-004.

- 3. MELTABLE RINGS: Thermally stabilized thermoplastic.
- 4. CONDUCTOR LEAD: MIL-W-81822-13 AWG26, solid, silver plated copper. Color: white.
- 5. GROUND LEAD: MIL-W-81822-13 AWG26, solid, silver plated copper. Color: blue.

## **APPLICATION**

- 1. This part is designed to provide an environment protected shield termination on cables, rated for 85°C minimum, meeting the dimensional requirements listed, having tin plated or bare copper shields.
- 2. Temperature range: -55°C to +125°C.
- 3. Install using TE Connectivity-approved convection or infrared tools in accordance with Raychem installation procedure RPIP-682-00.

For best results, prepare the cable as shown:



TE Connectivity, TE connectivity (logo), Raychem, Thermofit, and SolderSleeve are trademarks

= <u>TE</u>				THE	nychem RMOFIT EVICES		COAXIAL SOLDERSLEEVE DEVICE WITH PRE-INSTALLED SOLID WIRES - LOW TEMPERATURE					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.						DOCUMENT NO.: <b>B-026-26-02</b>						
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	this draw			ectivity reserves the right to amend ring at any time. Users should the suitability of the product for lication.			Revision:		Issue Date: March 2020			
DRAWN BY: DATE: M. FORONDA 05-Dec-		00	ECO: ECO-20-003573			SCALE: None	SIZE:	SHEET: 1 of 1				