## **CUSTOMER DRAWING**



Product Name	Component Dimensions				"GA"	Cable Dimensions				
	L	øA	øB	øC	Wire Gauge	øD	øE	øF	G±0.5	M±0.5
	max	min	min	min	(AWG)			min	(G±0.02)	(M±0.02)
B-040-20-N					20	1.70	1.50			
B-040-22-N					22	(0.065)	(0.060)			
B-040-24-N	30.0	4.40	2.80	1.60	24	to	to	0.30	16.0	6.0
B-040-26-N	(1.180)	(0.175)	(0.110)	(0.060)	26	4.40	2.80	(0.012)	(0.630)	(0.235)
B-040-28-N					28	(0.175)	(0.110)			
B-040-30-N					30					

## MATERIALS

- 1. & 5. INSULATION SLEEVE: Heat-shrinkable, radiation cross-linked modified polyvinylidene fluoride. Transparent blue.
- 2. & 4. SOLDER PREFORMS WITH FLUX:
  - SOLDER: TYPE Sn63 per ANSI J-STD-006.
  - FLUX: TYPE ROL0 per ANSI J-STD-004.
- 3. & 6. MELTABLE RINGS: Thermally stabilized thermoplastic.
- 7. CONDUCTOR LEAD: RAYCHEM 55A0111 in accordance with MIL-W-22759/32.See table for AWG.ETFE insulated, stranded tin plated copper.

Color: white.

8. GROUND LEAD: RAYCHEM 55A0111 in accordance with MIL-W-22759/32.See table for AWG.ETFE insulated, stranded tin plated. Copper.

Color: blue.

## APPLICATION

- 1. The parts covered by this document are for use in terminating the primary conductor and the braided shield of a coaxial cable having tin or silver-plated conductor and shield, rated for at least 125° C and meeting the dimensional requirements listed.
- 2. Parts will meet the requirements of Raychem Specification RT-1404 when installed per Raychem RPIP-500-03.
- 3. Temperature range: -55°C to +150°C.

For best results, prepare the cable as shown:



=1	E	TE Co	nnecti	vity		<b>aychem</b> roducts	TITLE : COAXIAL S WITH PRE			EVICE ANDED WIRES
UNLESS OTHERV INCHES DIMENS					ILLIMET	DOCUMENT NO.: B-040-GA-N				
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	drav			Connectivity reserves the right to amend this awing at any time. Users should evaluate the itability of the product for their application.			DOCUMENT REVISION: E		REVISION ISSUE DATE: 01-DEC-2021	
DRAWN BY: MALLIKA.I	DRAWN BY: DATE: MALLIKA.D 19-NOV		-2021	CAGE CO 0609			2: 1-128737	SCALE: None	SIZE: A	SHEET: 1 of 1

© 2000 - 2020 TE Connectivity Corporation. All Rights Reserved.

TE Connectivity, TE Connectivity (logo), Raychem and SolderSleeve are trademarks.