



ITEM	PART/DRG NO	QTY	DESCRIPTION
SEE NOTE 2 ↔	1	01-701-0025	4 M22x1.5 19 A/F 39.5 LONG BRASS MULTI-SHEAR BOLT
SEE NOTE 2 ↔	2	01-710-0062	4 UNIVERSAL 300mm² TOP INSERT x 27mm (1xM22) - BRIGHT TIN PLATED
	3	01-803-0016	4 ENGRAVING LABEL - WHITE/BLACK/WHITE - 80x35mm
SEE NOTE 2 ↔	4	01-803-0025	4 UNIVERSAL 300mm² PRESSURE PLATE (1 BOLT) SPECIAL FOR LINK BOXES - ELECTRO TIN PLATED
	5	01-807-0434	1 4-WAY LINK BOX ENCLOSURE SET - MK2 & MK3 LINKBOX (UR6045TMB)
	6	01-807-0442	1 LINK BOX ENCLOSURE 2-PIECE COVER 4-WAY (MK2 & MK3 LINKBOX)
SEE NOTE 1 ↔	7	01-811-0004	4 TERMINAL COVER (MK2 & MK3 LINKBOX)
	8	01-811-0057	4 UPPER HOUSING CUT-OUT COVER - MULTICABLE (MK2 LINK BOX)
SEE NOTE 2 ↔	9	02-402-0014	2 LV BRASS END TERMINATION - Ø12.0 BORE OFFSET PALM WITH Ø13.0 HOLE c/w SINGLE-SHEAR BOLTS
SEE NOTE 2 ↔	10	02-500-0066	2 BRASS CNE END TERMINATION - TYPE 3 WITH M12 BOTTOM & SIDE HOLES, MULTI-SHEAR BOLT, MOUNTING WASHERS & BOLT
SEE NOTE 2 ↔	11	BAH-018070055	4 BRASS WOVEN GAUZE 50 x 100mm, 60 MESH, 0.17mm WIRE
SEE NOTE 4 ↔	12	BAH-018070379	1 70mm² (19/2.14) CLASS 2 STRANDED SINGLE CORE COPPER CONDUCTOR - GREEN/YELLOW PVC 6491X H07V-R TO BS6004 x 1000mm LONG
	13	BAH-018070592	1 RECYCLED LDPE 4 WAY LINK BOX BASE PAD : 820mm X 670mm X 12mm THICK
	14	BAH-018110104	12 INJECTION MOULDED TERMINAL COVER LID (MK2 & MK3 LINKBOX)
	15	BAH-018110108	1 4-WAY VAC-FORMED DIVING BELL - MK3 LINK BOX
SEE NOTE 3 ↔	16	BAH-018110112	1 4-WAY DIVING BELL LOCKING BAR - MK3 LINKBOX
	17	BAH-018110113	1 ADJUSTMENT LOCKING COLLAR - MK3 LINKBOX
SEE NOTE 2 ↔	18	BAH-018110149	1 3 & 4-CORE MK3 LINKBOX INSTALLATION GUIDE - NEUTRAL AND / OR EARTH CONNECTIONS
SEE NOTE 5 ↔	19	BAH-018110161	2 LIFTING HANDLE FOR MK3 LINKBOX DIVING BELL
	20	BAH-028110096	1 300mm² 4-WAY 4-CORE UNTAILED MK2 LINK BOX BODY
	21	BAH-028110135	1 4-WAY LINK / ACCESSORY TOOLBOX ASSEMBLY - MK3 LINKBOX
	22	BAH-170400089	2 BLACK REFUSE SACK : 18" x 29" x 39" x 200 GAUGE

NOTES :

1. TERMINAL COVERS (x4) ARE NOT TO BE CLIPPED TO BACK PANEL.
2. ALL PARTS MARKED "SEE NOTE 2 ↔" ARE TO BE PACKED IN TOOLBOX.
3. ADD 15mm LONG BEAD OF LOCTITE 595 SUPERFIX CLEAR SILICONE (AVANTE PART 9A430) TO LOWER THREADED AREA OF LOCKING BAR PRIOR TO ASSEMBLY WITH LOCKING COLLAR. ONCE ADJUSTED WITH LOCKING BAR FITTED TO ENCLOSURE AND LOCKING COLLAR JUST MAKING CONTACT WITH DIVING BELL, ALLOW SILICONE TO CURE.
4. PART MARKED "SEE NOTE 4 ↔" TO BE COILED AND PACKED IN ENCLOSURE.
5. LIFTING HANDLES ARE TO BE ATTACHED TO DIVING BELL USING SOLVENT CEMENT (AVANTE PART 0A529).

D	BAH-018070592 (x1) WAS BAH-018070427 (x1)	BH-01155	24/03/16
C	BAH-018070427 (x1) WAS (x2)	BH-00901	18/07/13
B	BAH-018110027 (x4) REMOVED & REPLACED WITH BAH-018110104 (x12), NOTE 5 ADDED & BAH-018110161 (x2) ADDED	BH-00851	11/03/13
A	FIRST ISSUE	BH-00770	19/01/12
Revision	Description	Name/DMR	Date
Design/Drawn	D M EATON	Date	19-Jan-12
Scale	1:15	Scale (UOS)	
TCPN	CX5588-000	Part Weight	
Drawing/Part No	BAH-028110146	Drawing Type	CUSTOMER
Rev	D		



Material	VARIABLES	Part Description	- IF IN DOUBT ASK - DO NOT SCALE -
Finish	VARIABLES	300mm² 4-WAY 4-CORE UNTAILED MK3 LINKBOX	
Tolerances (UOS)	N/A	- STANDARD UK VERSION	
B&H Short Desc.	1705/34C		