




D

C

B


A



RECOMMENDED P.C.B LAYOUT
(COMPONENT SIDE)

- NOTES:
- 1,Current Rating: 3.0AMP
 - 2,Contact Resistance: 20mΩ Max
 - 3,Withstand Voltage: 1000V AC/DC
 - 4,Insulation Resistance: 1000MΩ Min
 - 5,Operation Temperature: -40℃ to +105℃
 - 6,Contact Material: Copper alloy
 - 7,Contact Plating: Gold or tin over nickel
 - 8,Insulator Material:
High Temperature Plastic, UL94V-O, BK

Recommended soldering process:
Wave Soldering,Peak temperature: 260℃,5s



TUBE	80	8-2271969-0
↑	↑	↑
TUBE	40	4-2271969-0
↑	↑	↑
TUBE	20	2-2271969-0
↑	↑	↑
TUBE	12	1-2271969-2
↑	↑	↑
TUBE	6	2271969-6
PACKING	PINS	PN
PRODUCT FAMILY TABLE		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL	FINISH
-	-

DWN	26JUL2018	FRANK FAN
CHK	26JUL2018	GEORGE FU
APVD	26JUL2018	MING SHI
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING		

TE Connectivity

2.54 MM PTICH MOUDLE
VERTICAL TH RECEPTACLE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=2271969	-
SCALE	1:1	SHEET 1 OF 1	REV A