

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

REVISIONS

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWN	09AUG2019	RV	DH

Ordering Information (All "X's" must be included to complete part number)

SCE	R	X	2	2	A	C	A
Series SCE True Off-delay Timer	Output Rating W = 10A (SPDT) X = 5A (DPDT)	Output 1 = SPDT (W) 2 = DPDT (W)	Operating Mode 2 = True Off-Delay	Operating Voltage (+10%, -15%) A = 120VAC, 50/60 Hz. / 125VDC E = 24VAC, 50/60 Hz. / 24VDC F = 48VAC, 50/60 Hz. / 48VDC	Timing Range A = 0.1 to 3 sec. B = 0.5 to 15 sec. C = 1 to 30 sec. E = 4 to 120 sec. G = 10 to 300 sec. L = 0.33 to 10 min.	Timing Adjustment A = Knob Adjust F = Fixed Times -Specify time delay in seconds per the following examples: XF9.000 = 9 sec. XF99.00 = 99 sec. XF999.0 = 9999 sec. XF1000 = 1000 sec.	Agency Recognition R = UL recognized

Wiring Diagrams (Bottom Views)
**Fixed Time
Or Knob Adjust**
**Fixed Time
Or Knob Adjust**
Outline Dimensions

ALL DIMENSIONS ARE IN INCHES[MM].

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RV	09AUG2019	TE TE Connectivity	
		CHK RV	09AUG2019		
		APVD DH	09AUG2019	NAME SCE SERIES TIME DELAY RELAY	
		PRODUCT SPEC			
		APPLICATION SPEC		RESTRICTED TO	
		WEIGHT			
MATERIAL		FINISH		SIZE A3	CAGE CODE -
				DRAWING NO C=SCE-SERIES	REV A
		CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1

1470-19 (1/15)