



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	12JUL2018	WQR	CW

NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 16 A
INSULATION RESISTANCE: >=400MΩ
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5-2.5 mm² (20-14 AWG)
CONTACT FINISH: GOLD PLATED
CONTACT TYPE: SCREW CONTACT


注释:
1. 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 16A
绝缘电阻: >=400MΩ
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500 次
接线范围: 0.5-2.5 mm² (20-14 AWG)
端子表面处理: 镀金
接线类型: 螺丝连接





SCALE 1:1




10X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5N.m
10X M3 螺丝, 推荐锁紧力矩0.5N.m



M4 SCREW RECOMMENDED
TIGHTENING TORQUE 1.2N.m
M4 螺丝, 推荐锁紧力矩1.2N.m



4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5N.m
4X M3 螺丝, 推荐锁紧力矩0.5N.m



PANEL CUT FOR INSERTS FOR USING
WITHOUT HOODS/ HOUSINGS
不用防护外壳时芯件的安装开孔图

T2010102101-100	HA-010-MG	HA-010 MALE INSERT, GOLD PLATING HA-010公插, 镀金
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12JUL2018 WENQING RAO	TE Connectivity		
		CHK 12JUL2018 GINO YAO			
		APVD 12JUL2018 CHRIS WANG			
		PRODUCT SPEC 108-137045			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME HA-010-MG		
		0 PLC ±-	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
		1 PLC ±-			
		2 PLC ±-	A300779C-T2010102101100		
		3 PLC ±-			
		4 PLC ±-	SCALE 3:2 SHEET 1 OF 1 REV A		
		ANGLES ±-			
MATERIAL		FINISH	Customer Drawing		
-		-			
-		-			